

SKINDICHT® BL-M ATEX

SKINDICHT® BL-M ATEX,



II / 2G+1D

DIN EN 60423

DIN IEC 62444

ETIM 5:

ETIM 5.0 Class-ID: EC000032

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000032

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SKINDICHT® BL-M ATEX

:	ETIM 6.0 Class :
:	CE 0637 Ex II 2G
:	Ex eb IIC Ex II 1D
:	Ex ta IIIC
:	IECEX IBE 13.0029X
:	:
:	O- : NBR
:	DIN EN 60079-0
:	DIN EN 60079-7
:	DIN EN 60079-31
가:	IP 68 - 5 bar
:	-30°C +90°C

가 VAT 가 가 .

(24.04.2024)



SKINDICHT® BL-M ATEX

	Article designation / size	SW (mm)	Thread length D mm	Ø (mm)	PU
SKINDICHT® BL-M ATEX					
52103103	M 12 x 1,5	16	5	17.8	50
52103113	M 16 x 1,5	20	5	22.0	50
52103123	M 20 x 1,5	24	6	26.4	50
52103133	M 25 x 1,5	29	7	31.9	50
52103143	M 32 x 1,5	36	8	39.6	25
52103153	M 40 x 1,5	45	8	49.5	25
52103163	M 50 x 1,5	54	9	59.0	10
52103173	M 63 x 1,5	67	10	73.5	10

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16