

## SKINDICHT® BL-M FKM

SKINDICHT® BL-M, brass bling plug with FKM o-ring to close unused threaded bore holes, mounting with screwdriver



가



-



Withstands temperatures up to +200 °C.

Simple assembly by using a slotted screwdriver.

Article numbers ending in "LF" are lead-free product alternatives with the same product properties. "Lead-free" articles do not contain lead, which is currently still allowed to make up to four percent in copper alloys. It could be banned in the future

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

## SKINDICHT® BL-M FKM

according to the RoHS Directive.

For closing an unoccupied metric threaded hole on the housing.  
Withstands high chemical and mechanical stress.

DIN EN 60423

DIN IEC 62444

ETIM 5:

ETIM 5.0 Class-ID: EC000032

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000032

ETIM 6.0 Class :

:

Body: nickel-plated brass

O-Ring: FKM

가:

IP66

IP 68 - 10 bar

:

-20°C +200°C

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

SKINDICHT® BL-M FKM

|            | Article designation / size | , C mm | Thread length D mm | Ø (mm) | / PU |
|------------|----------------------------|--------|--------------------|--------|------|
| 52123100   | M12x1,5                    | 7.5    | 5                  | 14.0   | 50   |
| 52123110   | M16x1,5                    | 8.0    | 5                  | 18.0   | 50   |
| 52123120   | M20x1,5                    | 9.5    | 6                  | 22.0   | 50   |
| 52123130   | M25x1,5                    | 11.0   | 7                  | 28.0   | 50   |
| 52123140   | M32x1,5                    | 12.0   | 8                  | 35.0   | 25   |
| 52123150   | M40x1,5                    | 13.0   | 9                  | 44.0   | 25   |
| 52123160   | M50x1,5                    | 15.0   | 9                  | 54.0   | 5    |
| 52123170   | M63x1,5                    | 16.0   | 10                 | 70.0   | 5    |
| 52123100LF | M12x1,5                    | 7.5    | 5                  | 14.0   | 50   |
| 52123110LF | M16x1,5                    | 8.0    | 5                  | 18.0   | 50   |
| 52123120LF | M20x1,5                    | 9.5    | 6                  | 22.0   | 50   |
| 52123130LF | M25x1,5                    | 11.0   | 7                  | 28.0   | 50   |
| 52123140LF | M32x1,5                    | 12.0   | 8                  | 35.0   | 25   |
| 52123150LF | M40x1,5                    | 13.0   | 9                  | 44.0   | 25   |
| 52123160LF | M50x1,5                    | 15.0   | 9                  | 54.0   | 5    |
| 52123170LF | M63x1,5                    | 16.0   | 10                 | 70.0   | 5    |