

SKINDICHT® SM-M INOX

SKINDICHT® SM-M INOX,



가

DIN EN 60423

DIN IEC 62444

ETIM 5:

ETIM 5.0 Class-ID: EC000940

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000940

ETIM 6.0 Class :

:

303

:

-60°C +200°C

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SKINDICHT® SM-M INOX

	Article designation / size	(mm)	SW (mm)	Ø (mm)	/ PU
SKINDICHT® SM-M INOX					
52032585	M 12 x 1,5	2.8	15	16.5	10
52032615	M 16 x 1,5	2.8	19	20.9	10
52032625	M 20 x 1,5	3.0	24	26.7	10
52032635	M 25 x 1,5	3.5	30	33.0	10
52032645	M 32 x 1,5	4.0	36	39.0	10
52032655	M 40 x 1,5	5.0	46	50.0	10
52032665	M 50 x 1,5	5.0	55	60.0	10
52032675	M 63 x 1,5	6.0	70	78.0	10

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16