

SKINDICHT® SM-M

SKINDICHT® SM-M,

Also available as lead-free version - the lead-free articles end on LF after the article number



가

DIN EN 60423

DIN IEC 62444

ETIM 5:

ETIM 5.0 Class-ID: EC000940

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000940

ETIM 6.0 Class :

:

:

-60°C +200°C

가 VAT 가 가 .

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

SKINDICHT® SM-M

	Article designation / size	(mm)	SW (mm)	Ø (mm)	/ PU
SKINDICHT® SM-M					
52102998	M 6 x 1	3.2	10	11.1	50
52102997	M 8 x 1	4.0	13	14.4	50
52102999	M 10 x 1	5.0	17	19.1	50
52103000	M 12 x 1,5	3.0	15	16.5	100
52103010	M 16 x 1,5	3.0	19	20.9	100
52103020	M 20 x 1,5	3.5	24	26.4	100
52103030	M 25 x 1,5	4.0	30	33.0	100
52103040	M 32 x 1,5	4.0	36	39.6	100
52103050	M 40 x 1,5	5.0	46	50.6	50
52103060	M 50 x 1,5	5.0	60	65.0	50
52103070	M 63 x 1,5	5.0	70	77.0	25
52103071	M 75 x 1,5	8.0	85	95.0	1
52103072	M 90 x 2	10.0	102	114.0	1
52103073	M 110 x 2	12.0	124	135.0	1
52103000LF	M 12 x 1,5	3.0	15	16.5	100
52103010LF	M 16 x 1,5	3.0	19	20.9	100
52103020LF	M 20 x 1,5	3.5	24	26.4	100
52103030LF	M 25 x 1,5	4.0	30	33.0	100
52103040LF	M 32 x 1,5	4.0	36	39.6	100
52103050LF	M 40 x 1,5	5.0	46	50.6	50
52103060LF	M 50 x 1,5	5.0	60	65.0	50
52103070LF	M 63 x 1,5	5.0	70	77.0	25