

SKINDICHT® VENT INOX

SKINDICHT® VENT STAINLESS STEEL,



Lapp



가

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

SKINDICHT® VENT INOX

UL 508 A

: 100mbar=0.4l/min -
: 100mbar=2.4l/min - UL

ETIM 5:

ETIM 5.0 Class-ID: EC000441
ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000441
ETIM 6.0 Class :

:

EN 60423

:

: -

:

303

O-ring - NBR

가:

Standard: IP66 / IP68 / IP69

UL: IP66 / IP67 / IP69

:

-40 °C~+105 °C

가 VAT 가 가 .

(24.04.2024)



SKINDICHT® VENT INOX

	Article designation / size	, C mm	Thread length D mm	/ PU
51730204	SKINDICHT® VENT INOX 12x1,5	21.0	10	10
cURus				
51730205	SKINDICHT® VENT INOX 12x1,5 plus	21.0	10	10

(24.04.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16