

SKINDICHT® E-M

SKINDICHT® E-M, , , 가



The various incisions can be easily taken out with a knife.

, SKINDICHT®

가 () 가 ,

ETIM 5:

ETIM 5.0 Class-ID: EC001181

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC001181

ETIM 6.0 Class :

:

CR

:

-20°C +80°C

:

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SKINDICHT® E-M

	Article designation / size	Ø x (mm)	(mm)	/ PU
SKINDICHT® E-M				
52100620	E-M 12	10.0 x 5	5.0	250
52100621	E-M 16	13.8 x 3/6/9	5.5	250
52100622	E-M 20	17.6 x 4/7/10/13	6.0	250
52100623	E-M 25	22.6 x 8.5/11.5/14.5/17.5	7.5	100
52100624	E-M 32	29.6 x 16/19/22/25	9.5	100
52100625	E-M 40	37.6 x 23/26/29/32	12.0	50
52100626	E-M 50	47.6 x 30/33/36/39	12.0	50
52100627	E-M 63	60.6 x 36/39/42/45	14.0	50

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16