

SKINDICHT® SHV cone seal

SKINDICHT® SHV cone seal



, SKINDICHT® SHV Neoprene® ,

SKINDICHT® SHV FKM

SKINDICHT® SHV FKM , ,

SKINDICHT®

가 () 가 ,

ETIM 5:

ETIM 5.0 Class-ID: EC000451
ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000451
ETIM 6.0 Class :

:

CR:
FKM:

:

CR
FKM

(24.04.2024)



SKINDICHT® SHV cone seal

:

CR: -20°C to +80°C
FKM: -20°C to +200°C

가 VAT 가 가 .

(24.04.2024)

SKINDICHT® SHV cone seal

	PG /	Ø (mm)	(mm)	/ PU
SKINDICHT® SHV CR				
52021120	SHV 7/ 5.0	5.0	13.8	100
52021130	SHV 9/ 6.0	6.0	14.8	100
52021140	SHV 9/ 7.0	7.0	14.8	100
52021150	SHV 11/ 7.0	7.0	17.5	100
52021160	SHV 11/ 9.0	9.0	17.0	100
52021180	SHV13.5/ 9.0	9.0	18.5	100
52021170	SHV13.5/ 11.0	11.0	18.5	100
52021190	SHV 16/ 11.0	11.0	19.5	50
52021200	SHV 16/ 13.0	13.0	19.5	50
52021210	SHV 16/ 15.0	15.0	19.5	50
52024460	SHV 21/ 16.0	16.0	19.8	50
52021220	SHV 21/ 18.0	18.0	19.8	50
52021230	SHV 21/ 20.0	20.0	19.8	50
52021240	SHV 29/ 22.0	22.0	24.0	25
52021250	SHV 29/ 24.0	24.0	24.0	25
52021260	SHV 29/ 26.0	26.0	24.0	25
SKINDICHT® SHV FKM				
52021259	SHV 7/ 5.0	5.0	13.8	100
52021146	SHV 9/ 6.0	6.0	14.8	100
52021261	SHV 9/ 7.0	7.0	14.8	100
52021262	SHV 11/ 7.0	7.0	17.5	100
52021263	SHV 11/ 9.0	9.0	17.0	100
52021271	SHV 13.5/ 9.0	9.0	18.5	100
52021272	SHV 13.5/ 11.0	11.0	18.5	100
52021265	SHV 16/ 13.0	13.0	19.5	50
52021269	SHV 16/ 15.0	15.0	19.5	50
52021268	SHV 21/ 18.0	18.0	19.5	50
52021266	SHV 21/ 20.0	20.0	19.8	50
52021267	SHV 29/ 22.0	22.0	19.8	50

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16