

## SKINDICHT® BL

SKINDICHT® BL, PG 가



## Œ₩



PG

ETIM 5:

ETIM 6:

가:

:

ETIM 5.0 Class-ID: EC000032

ETIM 5.0

ETIM 6.0 Class-ID: EC000032 ETIM 6.0 Class :

O-: NBR

IP 54

IP 68 (with O-ring)

With O-ring: -20°C to +100°C Without O-ring: -60°C to +200°C

(23.04.2024)

©2024 Lapp Group - all rights reserved. http://lappkorea.lappgroup.com data sheet PN 0456 / 02\_03.16



## SKINDICHT® BL

가 VAT 가 가 .

(23.04.2024)
©2024 Lapp Group - all rights reserved.
http://lappkorea.lappgroup.com
data sheet
PN 0456 / 02\_03.16

	Article designation / size	/ PU	
SKINDICHT® BL			
52002680	PG 7	100	
52003390	PG 9	100	
52003400	PG 11	100	
52003410	PG 13,5	100	
52003420	PG 16	100	
52003430	PG 21	50	
52003440	PG 29	50	
52003450	PG 36	25	
52003460	PG 42	10	
52002790	PG 48	10	
SKINDICHT® BL, O-			
54001610	PG 7	100	
54000071	PG 9	100	
54000040	PG 11	100	
54001630	PG 13,5	100	
54001640	PG 16	100	
54001660	PG 21	50	
54001620	PG 29	50	
54001650	PG 36	25	
54001670	PG 42	10	
54001680	PG 48	10	

