

SKINDICHT® SM

SKINDICHT® SM,

Available in sizes PG7 to PG48.

Article numbers ending in "LF" are lead-free product alternatives with the same product properties. "Lead-free" articles do not contain lead, which is currently still allowed to make up to four percent in copper alloys. It could be banned in the future according to the RoHS Directive.

For locking a SKINTOP® /SKINDICHT® cable gland on the inside of the application (e.g. housing).

For thin-walled housings without a thread, which only allow one through-hole.
Withstands high mechanical loads.

PG

ETIM 5:	ETIM 5.0 Class-ID: EC000940
	ETIM 5.0 :
ETIM 6:	ETIM 6.0 Class-ID: EC000940
	ETIM 6.0 Class :
:	
:	-60°C +200°C

가 VAT 가 가 .

(24.08.2024)

	Article designation / size	(mm)	SW (mm)	Far corner dimension	/ PU
SKINDICHT® SM					
52003490	PG 7	2.8	15	16.6	100
52003500	PG 9	2.8	18	20	100
52003510	PG 11	3.0	21	23.5	100
52003520	PG 13,5	3.0	23	25.5	100
52003530	PG 16	3.0	26	29	100
52003540	PG 21	3.5	32	35.5	50
52003550	PG 29	4.0	41	45	50
52003560	PG 36	5.0	51	56	25
52003570	PG 42	5.0	60	65	25
52003580	PG 48	5.5	64	69	25
52003490LF	PG 7	2.8	15	16.6	100
52003500LF	PG 9	2.8	18	20	100
52003510LF	PG 11	3.0	21	23.5	100
52003520LF	PG 13,5	3.0	23	25.5	100
52003530LF	PG 16	3.0	26	29	100
52003540LF	PG 21	3.5	32	35.5	50
52003550LF	PG 29	4.0	41	45	50
52003560LF	PG 36	5.0	51	56	25
52003570LF	PG 42	5.0	60	65	25
52003580LF	PG 48	5.5	64	69	25