

E+D 가 SKINDICHT® RWV-M

E+D 가 SKINDICHT® RWV-M,

, 가



가

DIN EN 60423

DIN IEC 62444

(24.04.2024)



E+D 가 SKINDICHT® RWV-M

: SKINDICHT® SM-M IP55.

For combination with other SKINDICHT® or SKINTOP® cable glands, we propose our SKINDICHT® RWV-M without incised sealing ring (E) and compression screw (D)

ETIM 5:	ETIM 5.0 Class-ID: EC000441
	ETIM 5.0 :
ETIM 6:	ETIM 6.0 Class-ID: EC000441
	ETIM 6.0 Class :
:	:
	8 :
가:	O- : NBR
:	IP 55
	-20°C +100°C

가 VAT 가 가 .

(24.04.2024)



E+D 가

SKINDICHT® RWV-M

	Article designation / size	B in mm	Thread length D mm	K	L	Ø G	SW1	Ø A1	SW2	Ø A2	/ PU
E+D 가 SKINDICHT® RWV-M											
52107801	M 12 x 1,5	21	11.5	5	20.5	8	14.0	16	17.0	18.9	25
52107811	M 16 x 1,5	23	11.5	5	23.5	12	18.0	20	22.0	24.5	25
52107821	M 20 x 1,5	28.5	12.5	5	28.5	15	22.0	24	27.0	30.1	25
52107831	M 25 x 1,5	30	13.5	5	31	20	27.0	29	32.0	35.7	10
52107841	M 32 x 1,5	36.5	13.5	5	33.5	27	34.0	33.5	41.0	45.6	10
52107851	M 40 x 1,5	43	15.5	5	43	35	42.0	43	46.0	50.6	5

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16