

SKINDICHT® SE-M

SKINDICHT® SE-M,



2 M20 x 1.5 - M25 x 1.5
4 M32 x 1.5

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SKINDICHT® SE-M

ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class :

:

:

:

: CR/NBR

O- : NBR

가:

IP 55

:

-20°C +80°C

가

VAT

가

가

.

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SKINDICHT® SE-M

	Article designation / size	ØF (mm)	(mm)	SW (mm)	, C mm	(mm)	/ PU
SKINDICHT® SE-M							
52108000	M 20 x 1,5	4/7/10/13	31	20	49.2	42.0	10
52108010	M 25 x 1,5	8.5/11.5/14.5/17.5	40	25	68.2	60.0	5
52108020	M 32 x 1,5	16/19/22/25	51.5	32	84.2	66.0	1

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16