

## SKINTOP® MULTI Flange FL21

SKINTOP® MULTI Flansch FL21, flange plate



Reduces the rectangular, standard FL21 mounting cut-out and allows flexibility when selecting the multi-cable entry system.  
Versatile use in various applications and environments.

Pre-assembled NBR seal enables reliable sealing to the housing (protection class IP 66).

Easy assembly with 4 fastening screws.

Stable construction made of powder-coated steel sheet or V2A stainless steel.

For cable entry into a housing with Scandinavian FL21 mounting cut-out, while simultaneously using the SKINTOP® MULTI or SKINTOP® CUBE multi-cable entry systems.

Can be used in dry, humid and oily environments.

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# SKINTOP® MULTI Flange FL21

: Steel plate, powder-coated  
Stainless steel  
Sealing: NBR

가: IP 66

: -10°C to +70 °C

가 VAT 가 가 .

(24.04.2024)



## SKINTOP® MULTI Flange FL21

	Article designation / size	Cut-out W x H	/ PU
52220030	Steel plate, powder-coated, RAL 7035	113.0 x 36.0	1
52220031	Stainless steel, V2A	113.0 x 36.0	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16