

SKINTOP® CUBE MULTI

SKINTOP® CUBE MULTI,

가



CE UK CA



Lapp



가

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SKINTOP® CUBE MULTI

SKINTOP®CUBE MULTI Version 1 : 9 x 3-6 mm 9 x 6-9 mm 2 x 9-13 mm
 1 x 13-16 mm
 SKINTOP®CUBE MULTI Version 2 : 23 x 5-8 mm

UL 50, UL 50E, CSA C22.2
 UL 508A(:)
 UL File No. E349737

SKINTOP® CUBE FRAME

SKINTOP® CUBE MULTI

24- (36 x 112 mm)

ETIM 5:

ETIM 5.0 Class-ID: EC000240

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000240

ETIM 6.0 Class :

:

UL File No. E349737

UL94 V-2

:

:

: 가

: CR

: PC / Gel

가:

IP 66

:

-30°C ~ +100°C

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



SKINTOP® CUBE MULTI

	Article designation / size	.	Number of cables x clamping range
SKINTOP® CUBE MULTI -			
52220050	SKINTOP® CUBE MULTI Version 1	21	9 x 3-6 mm; 9 x 6-9 mm; 2 x 9-13 mm; 1 x 13-16 mm
52220053	SKINTOP® CUBE MULTI Version 2	23	23 x 5-8 mm
SKINTOP® CUBE MULTI -			
52220056	SKINTOP® CUBE MULTI Version 1	21	9 x 3-6 mm; 9 x 6-9 mm; 2 x 9-13 mm; 1 x 13-16 mm
52220057	SKINTOP® CUBE MULTI Version 2	23	23 x 5-8 mm
SKINTOP® CUBE			
52220001	SKINTOP® CUBE FRAME 24	-	-

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

SKINTOP® CUBE MULTI



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16