

SKINTOP® MULTI-M

가

Still completely sealed? The round, screw-in multiple entry system inserts up to 30 cables simultaneously into an enclosure and seals them with IP68 protection. Thanks to the variable clamping range, you are completely flexible in your choice of cable diameters!



Lapp



(25.04.2024)

SKINTOP® MULTI-M



Multiple insertion of cables enables higher packing density (up to 30 cables depending on the variant).
 Large clamping ranges, each variable by 4 mm, for different cable diameters.
 Direct cable entry without pre-piercing the bushings.
 Flexibility in the choice of cable diameters reduces the variety of parts in the warehouse and provides logistical and cost advantages.
 Simple mounting on the enclosure by screw-in or fixing with locknut.

For sealing and strain-relieving multiple insertion of non-assembled cables through a housing.
 Can be used in dry, humid and oily environments.
 Suitable for outdoor use.

Unused feedthroughs remain securely closed and sealed thanks to elastic gel technology with innovative membrane technology.
 Best possible sealing to the housing and to the cables enables protection class IP 68.
 UL certification according to technical data enables use of the product in the North American region.

UL 50, UL 50E, CSA C22.2
 UL 508A(:)
 UL File No. E349737

SKINTOP® MULTI-M O

ETIM 5:	ETIM 5.0 Class-ID: EC000240
	ETIM 5.0 :
ETIM 6:	ETIM 6.0 Class-ID: EC000240
	ETIM 6.0 Class :
:	UL File No. E349737
	Fire behaviour acc. to UL94 V-2
	Hazard Level HL 2 acc. to EN 45545-2
:	:-
:	:
	:
	O-Ring: NBR
가:	IP 68
:	With O-ring: -20°C to +100°C
	Without O-ring: -30°C to +110°C



SKINTOP® MULTI-M

가 VAT 가 가 .

(25.04.2024)

	Article designation / size	.	x Ø /	SW (mm)	/ PU
52220140	M25x1,5	4	4 x 2-6 mm	30	1
52220143	M25x1,5	3	1 x 6-10mm, 2 x 2-6mm	30	1
52220146	M32x1,5	8	8 x 2-6mm	36	1
52220149	M32x1,5	6	3 x 6-10mm, 3 x 1-4mm	36	1
52220110	M40x1,5	12	2 x 1-4 mm, 10 x 2-6 mm	46	1
52220113	M40x1,5	6	5 x 6-10mm, 1 x 4-8mm	46	1
52220111	M50x1,5	18	18 x 2-6 mm	55	1
52220114	M50x1,5	8	8 x 6-10mm	55	1
52220112	M63x1,5	30	30 x 2-6 mm	66	1
52220115	M63x1,5	14	14 x 6-10mm	66	1

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

SKINTOP® MULTI-M



(25.04.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16