

# SKINTOP® SDV-M ATEX

SKINTOP® SDV-M ATEX



SKINTOP® SDV-M is used together with SKINTOP® MS-M ATEX, MS-M ATEX BRUSH or SKINTOP® K-M ATEX plus (blue)

II / 2G+1D

가 , SKINTOP® ST-M SKINTOP® MS-M

ETIM 5:	ETIM 5.0 Class-ID: EC000032
	ETIM 5.0 :
ETIM 6:	ETIM 6.0 Class-ID: EC000032
	ETIM 6.0 Class :
:	
:	CR
가:	IP 68 - 10 bar

(24.04.2024)



# SKINTOP® SDV-M ATEX

:

-30°C +70°C  
: +90°C

가 VAT 가 가 .

(24.04.2024)



SKINTOP® SDV-M ATEX

	Article designation / size	가 (mm)	/ PU
SKINTOP® SDV-M ATEX			
54113002	M 12 ATEX	3.0	50
54113012	M 16 ATEX	3.0	50
54113022	M 20 ATEX	3.5	50
54113032	M 25 ATEX	3.5	50
54113042	M 32 ATEX	4.0	25
54113052	M 40 ATEX	4.0	25
54113062	M 50 ATEX	4.5	10
54113072	M 63 ATEX	4.5	5

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16