

SKINTOP® SDVR-M ATEX

SKINTOP® SDV-M ATEX



SKINTOP® SDVR-M is used together with SKINTOP® MSR-M ATEX or SKINTOP® KR-M ATEX plus (blue)

II / 2G+1D

가 , SKINTOP® ST-M SKINTOP® MS-M

ETIM 5:	ETIM 5.0 Class-ID: EC000032
	ETIM 5.0 :
ETIM 6:	ETIM 6.0 Class-ID: EC000032
	ETIM 6.0 Class :
:	
:	CR
가:	IP 68 - 10 bar

(28.04.2024)



SKINTOP® SDVR-M ATEX

: -30°C +70°C
: +90°C

가 VAT 가 가 .

(28.04.2024)



SKINTOP® SDVR-M ATEX

	Article designation / size	가 (mm)	PU
SKINTOP® SDVR-M ATEX			
54113013	M 16 ATEX	4.0	50
54113023	M 20 ATEX	5.0	50
54113033	M 25 ATEX	5.0	50
54113043	M 32 ATEX	5.5	25

(28.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16