

# SKINTOP® ST-HF-M

SKINTOP® ST-HF-M, , ,

Hazard Level: HL 3



UL 94 V0

( )

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# SKINTOP® ST-HF-M

DIN EN 45545-2 (HL3)  
EN 60695-2-1/1 +960°C

DIN EN 60423  
DIN IEC 62444

ETIM 5: ETIM 5.0 Class-ID: EC000441  
ETIM 5.0 :

ETIM 6: ETIM 6.0 Class-ID: EC000441  
ETIM 6.0 Class :

: T21  
: (RAL 7035)  
Black (RAL 9005), UV-resistant

: : O-Ring:

가: IP 68 - 5 bar  
: -40°C +100°C  
: -20°C ~ +100°C

가 VAT 가 가 .

SKINTOP® ST-HF-M

	Article designation / size	Ø F mm	SW (mm)	, C mm	Thread length D mm	/ PU
SKINTOP® ST-HF-M						
53111407	M 12 x 1,5	4 - 5.5	15	30.0	8	100
53111417	M 16 x 1,5	4.5 - 9	19	34.0	8	100
53111427	M 20 x 1,5	7 - 13	25	37.0	9	100
53111437	M 25 x 1,5	9 - 17	30	40.0	10	50
53111447	M 32 x 1,5	11 - 21	36	47.0	10	25
53111457	M 40 x 1,5	19 - 28	46	52.0	10	10
53111467	M 50 x 1,5	27 - 35	55	62.0	12	5
53111477	M 63 x 1,5	34 - 45	66	71.0	12	5
SKINTOP® ST-HF-M						
53111408	M 12 x 1,5	4 - 5.5	15	30.0	8	100
53111418	M 16 x 1,5	4.5 - 9	19	34.0	8	100
53111422	M 20 x 1,5	7 - 13	25	37.0	9	100
53111438	M 25 x 1,5	9 - 17	30	40.0	10	50
53111448	M 32 x 1,5	11 - 21	36	47.0	10	25
53111458	M 40 x 1,5	19 - 28	46	52.0	10	10
53111468	M 50 x 1,5	27 - 35	55	62.0	12	5
53111478	M 63 x 1,5	34 - 45	66	70.0	12	5

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16