

SKINTOP® BS

SKINTOP® BS, (anti-kink)



VDE 0700-1

(23.04.2024)



SKINTOP® BS

UL E79903

DIN 40430 PG

가 SKINTOP® BSR 가

ETIM 5:	ETIM 5.0 Class-ID: EC000441
	ETIM 5.0 :
ETIM 6:	ETIM 6.0 Class-ID: EC000441
	ETIM 6.0 Class :
:	T21
:	(RAL 7001)
	(RAL 9005), UV-
:	:
	: CR
가:	IP 68 - 5 bar
:	-20°C +100°C

가 VAT 가 가 .

(23.04.2024)



SKINTOP® BS

	Article designation / size	Ø F mm	SW (mm)	, C mm	Thread length D mm	/ PU
53015600	PG 7	2.5 - 6.5	15	62.0	7.8	100
53015610	PG 9	3.5 - 8	19	75.0	8	100
53015620	PG 11	4 - 10	22	87.0	8	100
53015630	PG 13,5	6 - 12	24	100.0	9	50
53015640	PG 16	9 - 14	27	113.0	10	25
53015650	PG 21	13 - 18	33	129.0	11	25
53015800	PG 7	2.5 - 6.5	15	62.0	7.8	100
53015810	PG 9	3.5 - 8	19	75.0	8	100
53015820	PG 11	4 - 10	22	87.0	8	100
53015830	PG 13,5	6 - 12	24	100.0	9	50
53015840	PG 16	9 - 14	27	113.0	10	25
53015850	PG 21	13 - 18	33	129.0	11	25

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16