

SKINTOP® HYGIENIC / SKINTOP® HYGIENIC-R

SKINTOP® HYGIENIC / SKINTOP® HYGIENIC-R,

가

New: Available up to size M40x1,5

, 가 가

No gaps, voids or outer lying thread - so no risk of contamination of food machines, facilities or components



가

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

SKINTOP® HYGIENIC / SKINTOP® HYGIENIC-R

EHEDG (TYPE EL Class I AUX)

()

ECOLAB®

FDA 21 CFR 177.2600

DIN EN 1672-2

DIN EN ISO 14159

Security of machinery – Hygienic requirements for the design of machinery

NSF/ANSI 169 ,

DIN EN 60423

DIN IEC 62444

ETIM 5:

ETIM 5.0 Class-ID: EC000441

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC000441

ETIM 6.0 Class :

:

UL approval for M32x1,5 and M40x1,5 pending

:

: - V4A (1.4404/316L)

:

:

가:

IP 68 - 10 bar

IP 69

NEMA Type 1, 2, 4x, 6, 12

:

-20°C +100°C

가

가 VAT 가 가 .

(23.12.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

SKINTOP® HYGIENIC / SKINTOP® HYGIENIC-R

	Article designation / size	Ø F mm	SW (mm)	, C mm	Thread length D mm	/ PU
SKINTOP® HYGIENIC						
53105100	M 12 x 1,5	4 - 6	16	38.4	6.5	5
53105110	M 16 x 1,5	6.5 - 9	20	41.4	7	5
53105120	M 20 x 1,5	9 - 12	24	46.4	8	5
53105130	M 25 x 1,5	11.5 - 15.5	29	48.9	8	5
53105140	M 32 x 1,5	16 - 20	36	56.0	9	5
53105141	M 40 x 1,5	22 - 27	45	62.0	9	5
SKINTOP® HYGIENIC-R						
53105200	M 12 x 1,5	3 - 4.5	16	38.4	6.5	5
53105210	M 16 x 1,5	4.5 - 7	20	41.4	7	5
53105220	M 20 x 1,5	7 - 10	24	46.4	8	5
53105230	M 25 x 1,5	9 - 12.5	29	48.9	8	5
53105240	M 32 x 1,5	12.5 - 16.5	36	56.0	9	5
53105142	M 40 x 1,5	18 - 23	45	62.0	9	5

SKINTOP® HYGIENIC / SKINTOP® HYGIENIC-R

