


ETHERLINE® H Flex Cat.5e M12-RJ45

M12/RJ45

, Cat.5e, M12 RJ45, ,

가
www.lappgroup.com/assemblyfinderor

2170283







Lapp



가

2
CAT.5-

(24.04.2024)

ETHERLINE® H Flex Cat.5e M12-RJ45

EtherCAT EtherNet/IP

Cat.5e class D
2 : , 10/100Mbit/s

Braided conductor, 2x2x AWG26/7

:
:
: (RAL 5021)
D- M12 RJ45 가
4 M12

()

ETIM 5:

ETIM 5.0 Class-ID: EC002599

ETIM 5.0 class : ()

ETIM 6:

ETIM 6.0 Class-ID: EC002599

ETIM 6.0 Class :

:

: 15 x

: 6 x

가:

M12 - IP69

RJ45 - IP20

:

: -5 °C to +60 °C

: -30°C +80°C

, 가 가 (.) 가 .
가

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ETHERLINE® H Flex Cat.5e M12-RJ45

Article number		(m)	kg/1.000 pieces
R12	M12		
2171085	IE-5-M12D-S-1-H-2-26-7-RJ45	1	19
2171086	IE-5-M12D-S-2-H-2-26-7-RJ45	2	38
2171087	IE-5-M12D-S-3-H-2-26-7-RJ45	3	57
2171088	IE-5-M12D-S-5-H-2-26-7-RJ45	5	95
2171089	IE-5-M12D-S-10-H-2-26-7-RJ45	10	190
2171090	IE-5-M12D-S-20-H-2-26-7-RJ45	20	380
R12	M12		
2171878	IE-5-M12D-A-1-H-2-26-7-RJ45	1	19
2171879	IE-5-M12D-A-2-H-2-26-7-RJ45	2	38
2171880	IE-5-M12D-A-3-H-2-26-7-RJ45	3	57
2171881	IE-5-M12D-A-5-H-2-26-7-RJ45	5	95
2171883	IE-5-M12D-A-10-H-2-26-7-RJ45	10	190
2171885	IE-5-M12D-A-20-H-2-26-7-RJ45	20	380

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ETHERLINE® H Flex Cat.5e M12-RJ45



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16