

ETHERLINE® P Flex Cat.5e M12-RJ45

M12/RJ45
, Cat.5e, M12 RJ45, PUR,

가
www.lappgroup.com/assemblyfinderor







Lapp





ETHERLINE® P Flex Cat.5e M12-RJ45

EtherCAT EtherNet/IP

Cat.5e class D
2 : , 10/100Mbit/s

Braided conductor, 2x2x AWG26/7

PUR :
D- M12 (RAL 5021) RJ45 가
4 M12

ETIM 5: ETIM 5.0 Class-ID: EC002599
ETIM 5.0 class : ()
ETIM 6: ETIM 6.0 Class-ID: EC002599
ETIM 6.0 Class :
: 15 x
: 8 x
가: M12 - IP69
RJ45 - IP20
: -5 ° C ~ + 50 ° C (UL : + 80 ° C)
: -30°C +80°C

가 VAT 가 가 . 가 가 (.) 가 .



ETHERLINE® P Flex Cat.5e M12-RJ45

Article number		(m)	kg/1.000 pieces
R12	M12		
2171109	IE-5-M12D-S-1-P-2-26-7-RJ45	1	19
2171110	IE-5-M12D-S-2-P-2-26-7-RJ45	2	38
2171111	IE-5-M12D-S-3-P-2-26-7-RJ45	3	57
2171112	IE-5-M12D-S-5-P-2-26-7-RJ45	5	95
2171113	IE-5-M12D-S-10-P-2-26-7-RJ45	10	190
2171114	IE-5-M12D-S-20-P-2-26-7-RJ45	20	380
R12	M12		
2171887	IE-5-M12D-A-1-P-2-26-7-RJ45	1	19
2171888	IE-5-M12D-A-2-P-2-26-7-RJ45	2	38
2171889	IE-5-M12D-A-3-P-2-26-7-RJ45	3	57
2171890	IE-5-M12D-A-5-P-2-26-7-RJ45	5	95
2171892	IE-5-M12D-A-10-P-2-26-7-RJ45	10	190
2171894	IE-5-M12D-A-20-P-2-26-7-RJ45	20	380

(12.09.2023)

©2023 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ETHERLINE® P Flex Cat.5e M12-RJ45



(12.09.2023)

©2023 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16