

# ETHERLINE® PN Flex Cat.5 M12-RJ45

PROFINET

M12/RJ45

, Profinet Type B, Cat.5,

M12 on plug RJ45, PVC,

2170886

가

[www.lappgroup.com/assemblyfinderor](http://www.lappgroup.com/assemblyfinderor)



Lapp



가

2

EtherCAT EtherNet/IP

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16





ETHERLINE® PN Flex Cat.5 M12-RJ45

Article number		(m)	kg/1.000 pieces
R12	M12		
2171214	IE-PNB-5-M12D-S-0,5-Y-2-22-7-RJ45	0.5	15.65
2171215	IE-PNB-5-M12D-S-1-Y-2-22-7-RJ45	1	31.3
2171216	IE-PNB-5-M12D-S-2-Y-2-22-7-RJ45	2	62.6
2171217	IE-PNB-5-M12D-S-3-Y-2-22-7-RJ45	3	93.9
2171218	IE-PNB-5-M12D-S-5-Y-2-22-7-RJ45	5	156.5
2171219	IE-PNB-5-M12D-S-10-Y-2-22-7-RJ45	10	313
2171220	IE-PNB-5-M12D-S-20-Y-2-22-7-RJ45	20	626
R12	M12		
2171221	IE-PNB-5-M12D-A-0,5-Y-2-22-7-RJ45	0.5	15.65
2171222	IE-PNB-5-M12D-A-1-Y-2-22-7-RJ45	1	31.3
2171223	IE-PNB-5-M12D-A-2-Y-2-22-7-RJ45	2	62.6
2171224	IE-PNB-5-M12D-A-3-Y-2-22-7-RJ45	3	93.9
2171225	IE-PNB-5-M12D-A-5-Y-2-22-7-RJ45	5	156.5
2171226	IE-PNB-5-M12D-A-10-Y-2-22-7-RJ45	10	313
2171227	IE-PNB-5-M12D-A-20-Y-2-22-7-RJ45	20	626
RJ45	M12		
2171293	IE-PNB-5-M12DF-S-0,5-Y-2-22-7-RJ45	0.5	15.65
2171294	IE-PNB-5-M12DF-S-1-Y-2-22-7-RJ45	1	31.3
2171295	IE-PNB-5-M12DF-S-2-Y-2-22-7-RJ45	2	62.6
2171296	IE-PNB-5-M12DF-S-3-Y-2-22-7-RJ45	3	93.9
2171297	IE-PNB-5-M12DF-S-5-Y-2-22-7-RJ45	5	156.5

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

## ETHERLINE® PN Flex Cat.5 M12-RJ45



(24.04.2024)

©2024 Lapp Group - all rights reserved.  
<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16