

ETHERLINE® PN Flex Cat.5 RJ45

PROFINET

RJ45

, Profinet Type B, Cat.5, RJ45, PVC,

2170886

가

www.lappgroup.com/assemblyfinderor



Lapp



2

가

EtherCAT EtherNet/IP

(22.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ETHERLINE® PN Flex Cat.5 RJ45

Cat.5e class D
2 : , 10/100Mbit/s

: UL/CSA (CMG)

Braided conductor, 2x2x AWG22/7

:
PVC
: (RAL 6018)
RJ45 가

ETIM 5:	ETIM 5.0 Class-ID: EC002599
	ETIM 5.0 class : ()
ETIM 6:	ETIM 6.0 Class-ID: EC002599
	ETIM 6.0 Class :
	: 15 x
	: 10 x
가:	IP 20
	: -20°C to +60°C
	: -40°C +80°C

가 VAT 가 가 . (.) 가 .
가 가 가 가 .



ETHERLINE® PN Flex Cat.5 RJ45

Article number		(m)	kg/1.000 pieces
	RJ45 RJ45		
2171228	IE-PNB-5-RJ45-0,5-Y-2-22-7-RJ45	0.5	15.65
2171229	IE-PNB-5-RJ45-1-Y-2-22-7-RJ45	1	31.3
2171230	IE-PNB-5-RJ45-2-Y-2-22-7-RJ45	2	62.6
2171231	IE-PNB-5-RJ45-3-Y-2-22-7-RJ45	3	93.9
2171232	IE-PNB-5-RJ45-5-Y-2-22-7-RJ45	5	156.5
2171233	IE-PNB-5-RJ45-10-Y-2-22-7-RJ45	10	313
2171234	IE-PNB-5-RJ45-20-Y-2-22-7-RJ45	20	626
	RJ45		
2171235	IE-PNB-5-RJ45-0,5-Y-2-22-7-OE	0.5	15.65
2171236	IE-PNB-5-RJ45-1-Y-2-22-7-OE	1	31.3
2171237	IE-PNB-5-RJ45-2-Y-2-22-7-OE	2	62.6
2171238	IE-PNB-5-RJ45-3-Y-2-22-7-OE	3	93.9
2171239	IE-PNB-5-RJ45-5-Y-2-22-7-OE	5	156.5
2171240	IE-PNB-5-RJ45-10-Y-2-22-7-OE	10	313
2171241	IE-PNB-5-RJ45-20-Y-2-22-7-OE	20	626

(22.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16