

ETHERLINE® PN FD Cat.5 M12-RJ45

PROFINET

M12/RJ45

, Profinet Type C, Cat.5,

R12

M12, PUR,

2170894

가

www.lappgroup.com/assemblyfinderor



Lapp



가

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ETHERLINE® PN FD Cat.5 M12-RJ45

2

EtherCAT EtherNet/IP

Cat.5e class D
2 : , 10/100Mbit/s

UL/CSA (CMX)

Braided conductor, 2x2x AWG22/7

:
PUR
: (RAL 6018)
D- M12 RJ45 가
4 M12

ETIM 5:

ETIM 5.0 Class-ID: EC002599

ETIM 5.0 class : ()

ETIM 6:

ETIM 6.0 Class-ID: EC002599

ETIM 6.0 Class :

: 8 ×

가:

M12 - IP69

RJ45 - IP20

:

: -20°C +60°C

: -30°C +70°C

, 가 가 . (.) 가 .
가

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

ETHERLINE® PN FD Cat.5 M12-RJ45

Article number		(m)	kg/1.000 pieces
R12	M12		
2171264	IE-PNC-5-M12D-S-0,5-P-2-22-FD-RJ45	0.5	15.65
2171265	IE-PNC-5-M12D-S-1-P-2-22-FD-RJ45	1	31.3
2171266	IE-PNC-5-M12D-S-2-P-2-22-FD-RJ45	2	62.6
2171267	IE-PNC-5-M12D-S-3-P-2-22-FD-RJ45	3	93.9
2171268	IE-PNC-5-M12D-S-5-P-2-22-FD-RJ45	5	156.5
2171269	IE-PNC-5-M12D-S-10-P-2-22-FD-RJ45	10	313
2171270	IE-PNC-5-M12D-S-20-P-2-22-FD-RJ45	20	626
R12	M12		
2171271	IE-PNC-5-M12D-A-0,5-P-2-22-FD-RJ45	0.5	15.65
2171272	IE-PNC-5-M12D-A-1-P-2-22-FD-RJ45	1	31.3
2171273	IE-PNC-5-M12D-A-2-P-2-22-FD-RJ45	2	62.6
2171274	IE-PNC-5-M12D-A-3-P-2-22-FD-RJ45	3	93.9
2171275	IE-PNC-5-M12D-A-5-P-2-22-FD-RJ45	5	156.5
2171276	IE-PNC-5-M12D-A-10-P-2-22-FD-RJ45	10	313
2171277	IE-PNC-5-M12D-A-20-P-2-22-FD-RJ45	20	626

ETHERLINE® PN FD Cat.5 M12-RJ45



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16