

ETHERLINE® PN FD Cat.5 RJ45

PROFINET

RJ45

, Profinet Type C, Cat.5, RJ45, PUR,

2170894

가

www.lappgroup.com/assemblyfinderor



Lapp





ETHERLINE® PN FD Cat.5 RJ45

EtherCAT EtherNet/IP

Cat.5e class D
2 : , 10/100Mbit/s

UL/CSA (CMX)

Braided conductor, 2x2x AWG22/7

:
PUR : (RAL 6018)
RJ45 가

ETIM 5:	ETIM 5.0 Class-ID: EC002599
	ETIM 5.0 class : ()
ETIM 6:	ETIM 6.0 Class-ID: EC002599
	ETIM 6.0 Class :
:	: 8 x
가:	RJ45 - IP20
:	: -20°C to +60°C
	: -30°C +70°C

, 가 가 . (.) 가 .
 가 VAT 가 가 .



ETHERLINE® PN FD Cat.5 RJ45

Article number		(m)	kg/1.000 pieces
	RJ45 RJ45		
2171278	IE-PNC-5-RJ45-0,5-P-2-22-FD-RJ45	0.5	15.65
2171279	IE-PNC-5-RJ45-1-P-2-22-FD-RJ45	1	31.3
2171280	IE-PNC-5-RJ45-2-P-2-22-FD-RJ45	2	62.6
2171281	IE-PNC-5-RJ45-3-P-2-22-FD-RJ45	3	93.9
2171282	IE-PNC-5-RJ45-5-P-2-22-FD-RJ45	5	156.5
2171283	IE-PNC-5-RJ45-10-P-2-22-FD-RJ45	10	313
2171284	IE-PNC-5-RJ45-20-P-2-22-FD-RJ45	20	626
	RJ45		
2171285	IE-PNC-5-RJ45-0,5-P-2-22-FD-OE	0.5	15.65
2171286	IE-PNC-5-RJ45-1-P-2-22-FD-OE	1	31.3
2171287	IE-PNC-5-RJ45-2-P-2-22-FD-OE	2	62.6
2171288	IE-PNC-5-RJ45-3-P-2-22-FD-OE	3	93.9
2171289	IE-PNC-5-RJ45-5-P-2-22-FD-OE	5	156.5
2171290	IE-PNC-5-RJ45-10-P-2-22-FD-OE	10	313
2171291	IE-PNC-5-RJ45-20-P-2-22-FD-OE	20	626

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16