

# ETHERLINE® PN Cabinet Cat.6A

Cabinet Cord set for PROFINET-compliant installations inside the cabinet

Patchcords category 6A - for cabinet use in PROFINET applications

2170934



Lapp



Cat.6<sub>A</sub> acc. to ISO/IEC 11801  
 RJ45 acc. to IEC 60603-7-51  
 Cable offers AWM Style 21576, 80°C 1000V acc. to UL 758

, 4x2x AWG26/7

( )

S/FTP:

: PUR  
 : 6.4 mm  
 : (RAL 6018)

(24.08.2024)



# ETHERLINE® PN Cabinet Cat.6A

ETIM 5:

ETIM 5.0 Class-ID: EC002599

ETIM 5.0 class : ( )

:

: 4 x

: 8 x

가:

IP20

가 VAT 가 가 .

(24.08.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



## ETHERLINE® PN Cabinet Cat.6A

Article number		Length (m)	kg/1.000 pieces
2170570	ETHERLINE PN Cabinet Cat. 6a 0,25	0.25	7
2170571	ETHERLINE PN Cabinet Cat. 6a 0,5	0.5	14
2170572	ETHERLINE PN Cabinet Cat. 6a 1,0	1	28
2170573	ETHERLINE PN Cabinet Cat. 6a 1,5	1.5	42
2170574	ETHERLINE PN Cabinet Cat. 6a 2,0	2	56
2170575	ETHERLINE PN Cabinet Cat. 6a 2,5	2.5	70
2170576	ETHERLINE PN Cabinet Cat. 6a 3,0	3	84
2170577	ETHERLINE PN Cabinet Cat. 6a 4,0	4	112
2170578	ETHERLINE PN Cabinet Cat. 6a 5,0	5	140
2170579	ETHERLINE PN Cabinet Cat. 6a 10,0	10	-

(24.08.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16



## ETHERLINE® PN Cabinet Cat.6A



(24.08.2024)

©2024 Lapp Group - all rights reserved.  
<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16