

ETHERLINE® PN CAT.6A FD FC

Cat 6A, FC 가

class EA - 500MHz

Cat.6A

, 4 , PVC PUR - UL , 4x2xAWG24/7

CAT.6A: , 10Gbit/s
 PROFINET (4)
 FC



LAPP KABEL STUTTGART ETHERLINE® Cat.6, FD FC 4x2xAWG24/7



Lapp



(07.05.2024)

ETHERLINE® PN CAT.6A FD FC



4 : 가 100Mbit/s ~ 10Gbit/s

(,)

EtherCAT EtherNet/IP

PUR

ACC. IEC 60811-2-1

CAT.6A: , 10Gbit/s

CAT.6A, ISO/IEC 11801 EN 50173

IEC 61156-6

UL approvals see data sheet

IEC 60332-1-2

7-가

SF/UTP: , 2 , 4

: PUR, /PVC
: (RAL 6018)

ETIM 5:

ETIM 5.0 Class-ID: EC000830

ETIM 5.0 Class- :

() 125 V

: 15 x

: 8 x

/ : 1500 V AC

/ : 1000 V AC

100 Ohm

PVC: -40°C bis +80°C

PUR: -40°C bis +80°C

PVC: -10°C to +70°C

PUR: -30°C to +70°C

(07.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



ETHERLINE® PN CAT.6A FD FC

PROFINET® PNO (PROFIBUS) 가 가 . (.) 가 .
 가 . /
 가 VAT 가 가 .



ETHERLINE® PN CAT.6A FD FC

Article number		AWG	(mm)	mm	(kg/km)	(kg/km)
2170590	ETHERLINE PN Cat. 6A P FD FC	4x2xAWG24/7	1.05	8.9	52	106
2170591	ETHERLINE® PN Cat. 6A Y FD FC	4x2xAWG24/7	1.05	8.9	52	106

(07.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16