

UNITRONIC® BUS FF

가 FOUNDATION - UL

. UL / CSA . : -40 °C ~ + 105 °C



가



ISA/SP50

A FOUNDATION™ BUS

FOUNDATION™ BUS

UV-

UL / CSA (CMG / PLTC)

(23.04.2024)

UNITRONIC® BUS FF

3- (2-
3-)
: PVC, : PVC,

ETIM 5:	ETIM 5.0 Class-ID: EC000830
	ETIM 5.0 Class- :
ETIM 6:	ETIM 6.0 Class-ID: EC000830
	ETIM 6.0 Class :
:	300 V
:	24 Ohm/km
:	15 x
:	1500 V
..	100 ± 20 Ohm at 31.25 kHz
:	-40 °C -25 °C +105 °C,

가 가 (.) 가 .
www.lappkabel.de/en/cable-standradlengths
Foundation™ Fieldbus Foundation .
가 VAT 가 가 .



UNITRONIC® BUS FF

		/	(mm)	(kg/km)	(kg/km)
PVC					
2170352	UNITRONIC® BUS FF 2	1 x 2 x 1.1	7.9	39.7	82
2170350	UNITRONIC® BUS FF 3	1x2x1.1 + 1x1.1 Ø	7.9	48.3	93
PVC -					
2170351	UNITRONIC® BUS FF 3 ARM (YE)	1x2x1.1 + 1x1.1 Ø	12.3	125	182
2170353	UNITRONIC® BUS FF 3 ARM (BU)	1x2x1.1 + 1x1.1 Ø	12.3	125	182

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® BUS FF



(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16