

UNITRONIC® BUS PB FD FRNC FC

PROFIBUS - Fast Connect , UL/CSA
 PROFIBUS-DP, PROFIBUS-FMS FIP , UL/CSA , , , -40°C +80°C

LAPP KABEL STÜTGART UNITRONIC® BUS PB FD FRNC FC



(FC)
 PUR PROFIBUS-FMS FIP PROFIBUS-DP ()

()



UNITRONIC® BUS PB FD FRNC FC

Vertical Tray Flame Test according to UL 1685

PNO

(A, PROFIBUS-DP):

93.75 kbit/s = 1200 m

187.5 kbit/s = 1000 m

500 kbit/s = 400 m

1.5 Mbit/s = 200 m

12.0 Mbit/s = 100 m

The cable is UL/CSA-certified (CM)

: (O2YS)
:
: 가
: PUR, (RAL 4001)

ETIM 5: ETIM 5.0 Class-ID: EC000830
ETIM 5.0 Class- :
ETIM 6: ETIM 6.0 Class-ID: EC000830
ETIM 6.0 Class :
: 28nF/km
: () 250 V
: : 10 x
() : 15 x
: / : 1500 V
.: (3 - 20 MHz): 150 ± 15 Ohm
: : -30°C +70°C
: : -40°C +80°C

, 가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

Lapp Kabel PROFIBUS user organisation (PNO)

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



UNITRONIC® BUS PB FD FRNC FC

		() x () x (mm)	(mm)	(kg/km)
2170997	UNITRONIC® BUS PB FD FRNC FC	1x2x0,64	8	26

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16