

UNITRONIC® BUS PB FD P A

PROFIBUS - UL/CSA

PROFIBUS-DP, PROFIBUS-FMS FIP , UL/CSA , , -40°C
+80°C

: UL CSA

LAPP KABEL STUTTGART UNITRONIC® BUS PB FD P A



PUR 가 ()
PROFIBUS-FMS FIP PROFIBUS-DP .

PROFIBUS DP.(SIEMENS SIMATIC® NET, FIP 가 : DIN 19245 EN 50170 ,)

WTG((,))

: IEC 60332-1-2

PNO
(A, PROFIBUS-DP):

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® BUS PB FD P A

93.75 kbit/s = 1200 m
 187.5 kbit/s = 1000 m
 500 kbit/s = 400 m
 1.5 Mbit/s = 200 m
 12.0 Mbit/s = 100 m

: UL/CSA CMX UL 444 CSA C22.2 No.214

: (O2YS)
 :
 : PUR, (RAL 4001)

ETIM 5:	ETIM 5.0 Class-ID: EC000830
	ETIM 5.0 Class- :
ETIM 6:	ETIM 6.0 Class-ID: EC000830
	ETIM 6.0 Class :
:	(800 Hz): max. 30 nF/km
:	() 250 V
:	65 mm
:	/ : 1500 V
..	150 ± 15 Ohm
:	: -30°C +70°C
	: -40°C +80°C

, 가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
 : ≤ 30 kg or ≤ 250 m, . (e.g. 1 x 500 m or 5 x 100 m).
 SIMATIC® SIEMENS AG . FIP World FIP .
 Lapp Kabel PROFIBUS user organisation (PNO)
 가 VAT 가 가 .



UNITRONIC® BUS PB FD P A

		() x () x (mm)	(mm)	(kg/km)	(kg/km)
2170822	UNITRONIC® BUS PB FD P A	1 x 2 x 0.64	8	30.1	58