

# UNITRONIC® BUS PB FD P FC

PROFIBUS - Fast Connect , UL/CSA  
 PROFIBUS-DP, -FMS FIP , -40°C +80°C



PROFIBUS-FMS (FC) FIP PROFIBUS-DP

PROFIBUS DP.(SIEMENS SIMATIC® NET, FIP 가 : DIN 19245 EN 50170 )  
 ( , )

: IEC 60332-1-2

PNO  
 ( A, PROFIBUS-DP):  
 93.75 kbit/s = 1200 m  
 187.5 kbit/s = 1000 m  
 500 kbit/s = 400 m  
 1.5 Mbit/s = 200 m  
 12.0 Mbit/s = 100 m

: UL/CSA CMX UL 444 CSA C22.2 No.214



# UNITRONIC® BUS PB FD P FC

: (O2YS)  
 :  
 Fast Connect : PVC,  
 : PUR, (RAL 4001)

ETIM 5:	ETIM 5.0 Class-ID: EC000830
	ETIM 5.0 Class- :
ETIM 6:	ETIM 6.0 Class-ID: EC000830
	ETIM 6.0 Class :
:	(800 Hz): max. 30 nF/km
:	( ) 250 V
:	( ) : 15 x
:	3600 V DC (3 )
::	150 ± 15 Ohm
:	: -30°C +70°C
	: -40°C +80°C

, 가 가 . ( . ) 가 .  
 www.lappkabel.de/en/cable-standradlengths  
 : 30 kg or 250 m,  
 . (e.g. 1 x 500 m or 5 x 100 m ).  
 SIMATIC® SIEMENS AG . FIP World FIP .  
 Lapp Kabel PROFIBUS user organisation (PNO)  
 가 VAT 가 가 .



# UNITRONIC® BUS PB FD P FC

		( ) x ( ) x (mm)	(mm)	(kg/km)	(kg/km)
2170322	UNITRONIC® BUS PB FD P FC	1 x 2 x 0.64	8	26	79

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16