

## UNITRONIC® BUS PB FD Y HYBRID

PROFIBUS HYBRID , UL

PROFIBUS-DP, -FMS FIP , UV , -40°C +80°C



PROFIBUS-FMS ( , )  
FIP PROFIBUS-DP  
CL3

PROFIBUS DP.(SIEMENS SIMATIC® NET, 가 : DIN 19245 EN 50170 , )

HYBRID: +

With UL/CSA certification (CM, CL3, SUN RES, Oil Res I)  
CSA FT4 UL  
UL OIL RES I

(25.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# UNITRONIC® BUS PB FD Y HYBRID

1x2x0.64: , : Foam Skin PE 4x1.5: , , 1-4 : PVC  
: PVC, (RAL 4001)

|         |                             |
|---------|-----------------------------|
| ETIM 5: | ETIM 5.0 Class-ID: EC000830 |
|         | ETIM 5.0 Class- :           |
| ETIM 6: | ETIM 6.0 Class-ID: EC000830 |
|         | ETIM 6.0 Class :            |
| :       | 600 V ( )                   |
| :       | :                           |
|         | 5 x                         |
|         | : 15 x                      |
| :       | Core/core: 2000 V           |
|         | Core/screen: 2000 V         |
| ..      | 150 ± 15 Ohm                |
| :       | -5°C ~ +80°C                |

, 가 가 . ( . ) 가 .  
www.lappkabel.de/en/cable-standradlengths  
: ≤ 30 kg or ≤ 250 m,  
(e.g. 1 x 500 m or 5 x 100 m ).  
SIMATIC® SIEMENS AG . FIP World FIP .  
Lapp Kabel PROFIBUS user organisation (PNO)  
가 VAT 가 가 .

# UNITRONIC® BUS PB FD Y HYBRID

|         |                                  | (   ) x (   ) x<br>(mm)                  | (mm) | (kg/km) | (kg/km) |
|---------|----------------------------------|------------------------------------------|------|---------|---------|
| 2170882 | UNITRONIC® BUS PB FD Y<br>HYBRID | 1 x 2 x 0.64 Ø + 4 x 1.5 mm <sup>2</sup> | 11.3 | 89      | 155     |