

UNITRONIC® BUS LD FD P

PUR 가
 . Modbus, SUCOnet, Modulink, VariNet. , UL , DIN 47100. : -40 ° C +
 80 ° C

LD LAPP



RS485 / RS422
 () PUR

(,)
 ModBUS, SUCOnet P, Modulink P, VariNet-P) BUS

BUS ()
 9.6-93.75 kbit/s = 1200m
 187.5 kbit/s = . 1,000 m
 500 kbit/s = max. 400 m
 UV- (,)

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



UNITRONIC® BUS LD FD P

UNITRONIC®BUS LD FD P A: UL ; UL 444 CSA C22.2 No.214-02 UL/CSA CMX

: IEC 60332-1-2

DIN 47100

: PE

: PUR, (RAL 4001)

ETIM 5:

ETIM 5.0 Class-ID: EC000830

ETIM 5.0 Class- :

ETIM 6:

ETIM 6.0 Class-ID: EC000830

ETIM 6.0 Class :

:

(800 Hz) max. 60 nF/km

:

() 250 V

:

(): . 159.8 ohm/km

:

: 6 x

1 , :

3 x

: 15 x

:

/ : 1500 V

∴

100 - 120 Ohm

:

: -40°C +80°C

: -30°C +70°C

가 가 () 가
www.lappkabel.de/en/cable-standradlengths

: 30 kg or 250 m,

(e.g. 1 x 500 m or 5 x 100 m).

Modbus Modbus-IDA Organisation

.. SUCOnet P Moeller Group

. Modulink P

Weidmüller GmbH & Co.

. VariNet

Pepperl+Fuchs GmbH

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



UNITRONIC® BUS LD FDP

		mm ² /	(mm)	(kg/km)	(kg/km)
2170213	UNITRONIC® BUS LD FD P	1 x 2 x 0.25	6	18	39
2170214	UNITRONIC® BUS LD FD P	2 x 2 x 0.25	7.9	33	65
2170215	UNITRONIC® BUS LD FD P	3 x 2 x 0.25	8	39	77
- UL/CSA CMX					
2170813	UNITRONIC® BUS LD FD P A	1 x 2 x 0.25	6.2	18	39
2170814	UNITRONIC® BUS LD FD P A	2 x 2 x 0.25	8.3	33	65
2170815	UNITRONIC® BUS LD FD P A	3 x 2 x 0.25	8.4	39	77

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16