

UNITRONIC® CY PiDY (TP)

가

UNITRONIC® CY PiDY (TP): , PVC, , , , IEC

PiDY = PVC 가



- (TP) (Crosstalk)

: IEC 60332-1-2

VDE 0812

가

(24.04.2024)

UNITRONIC® CY PiDY (TP)

PVC

()
PVC

Outer sheath made of PVC

Outer sheath colour: grey (similar to pebble grey/ RAL 7032)

ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0
ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class :
:	DIN 47100, T9
:	C/C: 120nF/km C/S: 160nF/km
:	0.65 mH/km
:	, 가
:	: 6 x
:	< 160 Ohm/km
::	65 Ohm
:	: -5°C ~ +70°C : -40°C +80°C

가 가 () 가
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,
(e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(24.04.2024)



UNITRONIC® CY PiDY (TP)

	(mm ²)	(mm)	[kg/km]	[kg/km]
UNITRONIC® CY PiDY (TP)				
0034250	2 x 2 x 0.25	9.3	59.6	112
0034251	3 x 2 x 0.25	9.8	72.7	136
0034252	4 x 2 x 0.25	10.7	88.2	168
0034253	5 x 2 x 0.25	11.7	103.8	201
0034254	6 x 2 x 0.25	13.1	125.7	244
0034256	8 x 2 x 0.25	15.7	161	325
0034257	10 x 2 x 0.25	16.9	186.8	342
0034258	12 x 2 x 0.25	17.4	239.5	416
0034259	16 x 2 x 0.25	19.3	316.7	542

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16