



UNITRONIC® LiFYCY (TP)

UNITRONIC® LiFYCY (TP): PVC , , 0.08 mm² , , , IEC



- (TP) (Crosstalk)

가 : microelectronics, hearing aids etc.

: IEC 60332-1-2

PVC
TP

Outer sheath made of PVC
Outer sheath colour: grey (similar to pebble grey/ RAL 7032)

(05.05.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>
data sheet

PN 0456 / 02_03.16

UNITRONIC® LiFYCY (TP)

ETIM 5:	ETIM 5.0 Class-ID: EC000104 ETIM 5.0
ETIM 6:	ETIM 6.0 Class-ID: EC000104 ETIM 6.0 Class :
:	DIN 47100, T9
:	C/C approx. 80 nF/km C/S approx. 120 nF/km
:	At 1 kHz: approx. 300 pF/100 m
:	0.65 mH/km
:	- ' - ' , 0.08 mm ²
:	: 7.5 x
:	: 4 x
:	: -5°C ~ +70°C
:	: -40°C +80°C

가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
 : 30 kg or 250 m,
 . (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .



UNITRONIC® LIFYCY (TP)

	(mm ²)	(mm)	[kg/km]	[kg/km]
UNITRONIC® LIFYCY (TP)				
0034231	4 x 2 x 0.08	5.4	19.4	37
0034233	8 x 2 x 0.08	7.1	23.7	76

(05.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16