

JE-LiYCY...BD

JE-LiYCY ... BD - , VDE 0815, 7 , , PVC

DIN VDE 0815



- (TP) (Crosstalk)

JE-LiYCY ... BD 가

2- (2 x 2 x 0.5) 가
: IEC 60332-1-2

JE-LiYCY ... BD EB:

IEC 60079-14: 2013/EN 60079-14: 2014/VDE 0165-1: 2014, 16.2.2

(i-) ,

DIN VDE 0815
JE-LiYCY...BD

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

JE-LiYCY...BD

7-가

PVC

2 cores twisted into a pair, and 4 pairs into units/ bundles (for 2 x 2 x 0.5 as star quad cable)

Outer sheath made of PVC

Outer sheath colour: grey (similar to pebble grey/ RAL 7032)

ETIM 5:	ETIM 5.0 Class-ID: EC000829
	ETIM 5.0 : /
ETIM 6:	ETIM 6.0 Class-ID: EC000829
	ETIM 6.0 Class :
:	VDE 0815, T10
:	. 100 nF/km
:	200pF/100m
:	0.65 mH/km
:	, 7 x 0.3mm
:	: 15 x
:	: 5 x
:	Core/core: 500 V
:	Core/screen: 2000 V
:	. 78.4 ohm/km
:	Occasional flexing: -5°C ~ +50°C
:	: -30°C +70°C

가 가 () 가
www.lappkabel.de/en/cable-standradlengths
 : 30 kg or 250 m,
 . (e.g. 1 x 500 m or 5 x 100 m).

가 VAT 가 가 .

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

	(mm ²) /	(mm)	(kg/km)	(kg/km)
JE-LiYCY...BD				
0034200	2 x 2 x 0.5	6.6	51	70
0034201	4 x 2 x 0.5	8.5	87	155
0034202	8 x 2 x 0.5	11.7	144	260
0034208	12 x 2 x 0.5	12.8	195	340
0034203	16 x 2 x 0.5	13.9	249	430
0034210	20 x 2 x 0.5	15.1	298	495
0034204	24 x 2 x 0.5	16.4	348	605
0034212	32 x 2 x 0.5	21	441	738

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16