



UNITRONIC® LiYCY A

DIN 47100-UL/CSA 가
 UNITRONIC® LiYCY A: PVC , DIN 47100, UL CSA AWM, Flexible, 0.34² Maxi TERMI-POINT®,
 : UL CSA 가



UL-/CSA 가 ,

IEC 60332-1-2, UL VW-1 CSA FT 1

UL AWM Style 2464
 CSA AWM I/II A
 UL File No. E63634

PVC

(23.04.2024)

UNITRONIC® LiYCY A

PVC : (RAL 7005)

ETIM 5: ETIM 5.0 Class-ID: EC000104
ETIM 5.0

ETIM 6: ETIM 6.0 Class-ID: EC000104
ETIM 6.0 Class :

: DIN 47100 , T9

: AWG , 7 19

: : 15 x

: 6 x

: UL/CSA: 300 V

: 1500 V

: Occasional flexing: -5°C up to +70°C (UL: +80 °C)

Fixed installation (IEC): -40°C bis +80°C

UL: max. +80°C

가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 152 m; 305 m

가 VAT 가 가 .

UNITRONIC® LIYCY A

	AWG /	(mm)	[kg/km]	[kg/km]
UNITRONIC® LIYCY A				
0044602	2 x AWG26/7	4.3	15.6	25
0044604	4 x AWG26/7	4.7	18	30
0044652	2 x AWG24/7	4.7	17.6	29
0044655	5 x AWG24/7	5.5	28.5	44
0044658	8 x AWG24/7	6.4	31.1	61
0044662	12 x AWG24/7	7.3	51.8	96
0044702	2 x AWG22/7	5.5	17.6	44
0044703	3 x AWG22/7	5.7	21.2	49
0044704	4 x AWG22/7	6.1	27.3	59
0044705	5 x AWG22/7	6.6	30.8	63
0044707	7 x AWG22/7	7.1	46.4	87
0044712	12 x AWG22/7	8.9	66.8	120
0044716	16 x AWG22/7	9.8	83.9	145
0044721	21 x AWG22/7	11.3	109.4	204
0044732	2 x AWG20/7	6	24.4	41
0044733	3 x AWG20/7	6.3	29.9	47
0044735	5 x AWG20/7	7.3	49.2	91
0044738	8 x AWG20/7	9.1	70.8	102
0044850	7 x AWG18/19	8.9	93.2	160.8
0044851	10 x AWG18/19	11.5	130.9	200

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16