



UNITRONIC® LiYY A

DIN 47100 - UL/CSA

UNITRONIC® LiYY A: PVC , DIN 47100 , UL CSA AWM, (0.34² Maxi TERMI-POINT®),

: UL CSA
가 가



UL-/CSA 가 ,

IEC 60332-1-2, UL VW-1 CSA FT 1

UL AWM Style 2464
CSA AWM I/II A
UL File No. E63634

PVC
PVC : (RAL 7005)

UNITRONIC® LiYY A

ETIM 5:	ETIM 5.0 Class-ID: EC000104
	ETIM 5.0
ETIM 6:	ETIM 6.0 Class-ID: EC000104
	ETIM 6.0 Class :
:	DIN 47100 , T9
:	AWG , 7 19
:	: 15 x
	: 4 x
:	UL/CSA: 300 V
:	1500 V
:	Occasional flexing: -5°C up to +70°C (UL: +80 °C)
	Fixed installation (IEC): -40°C bis +80°C
	UL: max. +80°C

가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 152 m; 305 m
가 VAT 가 가 .

UNITRONIC® LIYY A

	AWG /	(mm)	[kg/km]	[kg/km]
UNITRONIC® LIYY A				
0022403	3 x AWG26/7	3.8	4.2	18
0022404	4 x AWG26/7	4	5.6	23
0022405	5 x AWG26/7	4.3	7	25
0022408	8 x AWG26/7	5.1	11.2	34
0022412	12 x AWG26/7	5.8	16.8	47
0022416	16 x AWG26/7	6.3	22.4	58
0022421	21 x AWG26/7	7	29.4	63
0022502	2 x AWG24/7	4	4.6	20
0022505	5 x AWG24/7	4.8	11.5	32
0022508	8 x AWG24/7	5.7	18.4	46
0022512	12 x AWG24/7	6.6	27.6	64
0022602	2 x AWG22/7	4.8	6.8	32.8
0022603	3 x AWG22/7	5	10.2	35
0022604	4 x AWG22/7	5.4	13.6	45.9
0022605	5 x AWG22/7	5.9	17	55.8
0022607	7 x AWG22/7	6.4	23.3	68.9
0022608	8 x AWG22/7	6.9	27.2	75.5
0022612	12 x AWG22/7	8.2	40.8	103
0022616	16 x AWG22/7	9.1	54.4	131.2
0022624	24 x AWG22/7	11.6	81.6	190
0022632	2 x AWG20/7	5.3	11.2	40
0022642	2 x AWG19/19	5.6	15	48