

UNITRONIC® ROBUST S/A FD

가 / M8, M12

Good chemical resistance please see Appendix T1
(Weather Resistance)



Lapp



(23.04.2024)

UNITRONIC® ROBUST S/A FD



가 , UV

가

EN 50396 HD 605 S2 /UV /

ECOLAB®

: PE

Colour-code: 3-pin: bn, bu, bk 4-pin: bn, wh, bu, bk 5-pin: bn, wh, bu, bk, gy

TPE

:

ETIM 5:

ETIM 5.0 Class-ID: EC001578

ETIM 5.0 Class 가

ETIM 6:

ETIM 6.0 Class-ID: EC001578

ETIM 6.0 Class :

:

acc. to EN 60947-5-2

:

VDE 0295 class 6, IEC 60228 class 6 가

:

: 5 x

: 3 x

:

: -40°C ~ +90°C

: -50°C ~ +90°C

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



UNITRONIC® ROBUST S/A FD

가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
가

가 VAT 가 가 .

(23.04.2024)



UNITRONIC® ROBUST S/A FD

		Dimensions (mm ²)	(mm)		[kg/km]
7038897	UNITRONIC ROBUST S/A FD 4X0,25	4x0.25	4.9		10.2
7038895	UNITRONIC ROBUST S/A FD 3X0,34	3 x 0.34	5		9.8
7038894	UNITRONIC ROBUST S/A FD 4X0,34	4 x 0.34	5.4		13.1
7038896	UNITRONIC ROBUST S/A FD 5X0,34	5 x 0.34	5.9		16

(23.04.2024)

©2024 Lapp Group - all rights reserved.
<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16