

# UNITRONIC® SENSOR M12-M8

M12 (M8 )  
 / , M8 3/4 , M12 , A-codiert, PUR LSZH, IP65 / IP67 / IP68,

[www.lappgroup.com/assemblyfinder](http://www.lappgroup.com/assemblyfinder) 가



Lapp



Space-saving due to compact dimensions.

( 가 )  
 가

가 가

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# UNITRONIC® SENSOR M12-M8

UV-

PWIS PVC

DIN VDE 0472  
UL : E249137  
: UL 1581 FT-2

: 0.25 mm<sup>2</sup>

: 3-pin: bn (1), bu (3), bk (4) 4-pin: bn (1), wh (2), bu (3), bk (4)  
: PUR,

ETIM 5:	ETIM 5.0 Class-ID: EC001855
	ETIM 5.0 Class: -
ETIM 6:	ETIM 6.0 Class-ID: EC001855
	ETIM 6.0 Class :
:	: CuSn : Ni/Au ,
	: TPU, ,
:	: 5 x
	: 10 x
가:	IP65/IP67/IP68
( ):	Plug/socket -25°C to +90°C
	-40°C - +80°C
	-25°C - +80°C
:	A-Standard
(A):	4 A

, 가 가 . ( . ) 가 .

가 VAT 가 가 .  
UL-Zertifizierungen sind dem Datenblatt zu entnehmen

(24.04.2024)



UNITRONIC® SENSOR M12-M8

		(m)	Design	LED	(V)	PU
22260225	AB-C3-M12MS-0,3PUR-M8FS	0.3	-	no	60	1
22260226	AB-C3-M12MS-0,6PUR-M8FS	0.6	-	no	60	1
22260227	AB-C3-M12MS-1,0PUR-M8FS	1	-	no	60	1
22260228	AB-C3-M12MS-2,0PUR-M8FS	2	-	no	60	1
22260229	AB-C3-M12MS-0,3PUR-M8FA	0.3	-	no	60	1
22260230	AB-C3-M12MS-0,6PUR-M8FA	0.6	-	no	60	1
22260231	AB-C3-M12MS-1,0PUR-M8FA	1	-	no	60	1
22260232	AB-C3-M12MS-2,0PUR-M8FA	2	-	no	60	1
22260267	AB-C3-M12MS-0,3PUR-M8FA-2L	0.3	-	2 LEDs	24	1
22260268	AB-C3-M12MS-0,6PUR-M8FA-2L	0.6	-	2 LEDs	24	1
22260269	AB-C3-M12MS-1,0PUR-M8FA-2L	1	-	2 LEDs	24	1
22260270	AB-C3-M12MS-2,0PUR-M8FA-2L	2	-	2 LEDs	24	1
4-						
22260347	AB-C4-M12MS-0,3PUR-M8FS	0.3	-	no	30	1
22260349	AB-C4-M12MS-0,6PUR-M8FS	0.6	-	no	30	1
22260350	AB-C4-M12MS-1,0PUR-M8FS	1	-	no	30	1
22260348	AB-C4-M12MS-2,0PUR-M8FS	2	-	no	30	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16