

# UNITRONIC® SENSOR M12

M12 /  
/ , 3 , M12 / M12 , A-codiert, PUR LSZH, IP65 / IP67 / IP68,

[www.lappgroup.com/assemblyfinder](http://www.lappgroup.com/assemblyfinder) 가



Lapp



Space-saving due to compact dimensions.

( )  
가

가 가

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# UNITRONIC® SENSOR M12

UV-

PWIS PVC

DIN VDE 0472  
UL : E249137  
: UL 1581 FT-2

: 0,34 mm<sup>2</sup>(8- : 0,25 mm<sup>2</sup>)

: 3 : bn (1), bu (3), bk (4) 4 : bn (1), wh (2), bu (3), bk (4) 5 : (1), bn (2), gn (3), ye4), gy (1), wh (2), bu (3), bk  
5), pk (6), bu (7), rd (8)  
: PUR,

ETIM 5: ETIM 5.0 Class-ID: EC001855  
ETIM 5.0 Class: -

ETIM 6: ETIM 6.0 Class-ID: EC001855  
ETIM 6.0 Class :

: : CuSn : Ni/Au ,  
: TPU, ,  
: 5 x  
: 10 x

가: IP65/IP67  
( ): Plug/socket -25°C to +90°C  
-40°C - +80°C  
-25°C - +80°C  
: A-Standard  
(A): 4 A  
2 A (8-pin)

, 가 가 . ( . ) 가 .

가 VAT 가 가 .  
UL-Zertifizierungen sind dem Datenblatt zu entnehmen

(24.04.2024)

		/	(m)	Design	LED	(V)	PU
22260221	AB-C3-M12MS-2,0PUR	3	2		no	250	1
22260222	AB-C3-M12MS-5,0PUR	3	5		no	250	1
22260249	AB-C3-M12MS-10,0PUR	3	10		no	250	1
22260223	AB-C3-M12MA-2,0PUR	3	2		no	250	1
22260224	AB-C3-M12MA-5,0PUR	3	5		no	250	1
22260256	AB-C3-M12MA-10,0PUR	3	10		no	250	1
22260257	AB-C3-2,0PUR-M12FS	3	2		no	250	1
22260250	AB-C3-5,0PUR-M12FS	3	5		no	250	1
22260251	AB-C3-10,0PUR-M12FS	3	10		no	250	1
22262142	AB-C3-15,0PUR-M12FS	3	15		no	250	1
22262143	AB-C3-25,0PUR-M12FS	3	25		no	250	1
22260252	AB-C3-2,0PUR-M12FS-2L	3	2		2 LEDs	24	1
22260265	AB-C3-5,0PUR-M12FS-2L	3	5		2 LEDs	24	1
22260266	AB-C3-10,0PUR-M12FS-2L	3	10		2 LEDs	24	1
22260258	AB-C3-2,0PUR-M12FA	3	2		no	250	1
22260259	AB-C3-5,0PUR-M12FA	3	5		no	250	1
22260260	AB-C3-10,0PUR-M12FA	3	10		no	250	1
22260253	AB-C3-2,0PUR-M12FA-2L	3	2		2 LEDs	24	1
22260254	AB-C3-5,0PUR-M12FA-2L	3	5		2 LEDs	24	1

UNITRONIC® SENSOR M12

		/	(m)	Design	LED	(V)	PU
22260255	AB-C3-10,0PUR-M12FA-2L	3	10		2 LEDs	24	1
22260320	AB-C4-M12MS-2,0PUR	4	2		no	250	1
22260321	AB-C4-M12MS-5,0PUR	4	5		no	250	1
22260342	AB-C4-M12MS-10,0PUR	4	10		no	250	1
22261066	AB-C4-M12MS-20,0PUR	4	20		no	250	1
22260301	AB-C4-M12MA-2,0PUR	4	2		no	250	1
22260302	AB-C4-M12MA-5,0PUR	4	5		no	250	1
22260303	AB-C4-M12MA-10,0PUR	4	10		no	250	1
22260322	AB-C4- 2,0PUR-M12FS	4	2		no	250	1
22260323	AB-C4- 5,0PUR-M12FS	4	5		no	250	1
22260343	AB-C4-10,0PUR-M12FS	4	10		no	250	1
22262131	AB-C4-15,0PUR-M12FS	4	15		no	250	1
22260933	AB-C4-20,0PUR-M12FS	4	20		no	250	1
22260377	AB-C4-25,0PUR-M12FS	4	25		no	250	1
22260344	AB-C4- 2,0PUR-M12FS-2L	4	2		2 LEDs	24	1
22260345	AB-C4- 5,0PUR-M12FS-2L	4	5		2 LEDs	24	1
22260346	AB-C4-10,0PUR-M12FS-2L	4	10		2 LEDs	24	1
22260911	AB-C4-15,0PUR-M12FS-2L	4	15		2 LEDs	24	1
22260324	AB-C4- 2,0PUR-M12FA	4	2		no	250	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# UNITRONIC® SENSOR M12

		/	(m)	Design	LED	(V)	PU
22260325	AB-C4- 5,0PUR-M12FA	4	5		no	250	1
22260341	AB-C4-10,0PUR-M12FA	4	10		no	250	1
22260326	AB-C4- 2,0PUR-M12FA-3L	4	2		3 LEDs	24	1
22262068	AB-C4- 3,0PUR-M12FA-3L	4	3		3 LEDs	24	1
22260327	AB-C4- 5,0PUR-M12FA-3L	4	5		3 LEDs	24	1
22260340	AB-C4-10,0PUR-M12FA-3L	4	10		3 LEDs	24	1
22260891	AB-C4- 15,0PUR-M12FA-2L	4	15		3 LEDs	24	1
22260947	AB-C4- 20,0PUR-M12FA-3L	4	20		3 LEDs	24	1
22262029	AB-C4- 25,0PUR-M12FA-3L	4	25		3 LEDs	24	1
22260819	AB-C4-30,0PUR-M12FA-3L	4	30		3 LEDs	24	1
22260892	AB-C4-35,0PUR-M12FA-3L	4	35		3 LEDs	24	1
22260400	AB-C5-M12MS-2,0PUR	5	2		no	60	1
22260401	AB-C5-M12MS-5,0PUR	5	5		no	60	1
22260414	AB-C5-M12MS-10,0PUR	5	10		no	60	1
22260402	AB-C5-M12MA-2,0PUR	5	2		no	60	1
22260403	AB-C5-M12MA-5,0PUR	5	5		no	60	1
22260417	AB-C5-M12MA-10,0PUR	5	10		no	60	1
22260404	AB-C5- 2,0PUR-M12FS	5	2		no	60	1
22260405	AB-C5- 5,0PUR-M12FS	5	5		no	60	1
22260415	AB-C5-10,0PUR-	5	10		no	60	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

UNITRONIC® SENSOR M12

		/	(m)	Design	LED	(V)	PU
	M12FS						
22260829	AB-C5-20,0PUR-M12FS	5	20		no	60	1
22262018	AB-C5-25,0PUR-M12FS	5	25		no	60	1
22260406	AB-C5- 2,0PUR-M12FA	5	2		no	60	1
22260407	AB-C5- 5,0PUR-M12FA	5	5		no	60	1
22260418	AB-C5-10,0PUR-M12FA	5	10		no	60	1
22260408	AB-C5- 2,0PUR-M12FA-3L	5	2		3 LEDs	24	1
22260409	AB-C5- 5,0PUR-M12FA-3L	5	5		3 LEDs	24	1
22260416	AB-C5-10,0PUR-M12FA-3L	5	10		3 LEDs	24	1
22260760	AB-C5-25,0PUR-M12FA-3L	5	25		3 LEDs	24	1
22260091	AB-C8-M12MS-2,0PUR	8	2		no	30	1
22260092	AB-C8-M12MS-5,0PUR	8	5		no	30	1
22260093	AB-C8-M12MS-10,0PUR	8	10		no	30	1
22260094	AB-C8-M12MA-2,0PUR	8	2		no	30	1
22260095	AB-C8-M12MA-5,0PUR	8	5		no	30	1
22260096	AB-C8-M12MA-10,0PUR	8	10		no	30	1
22260726	AB-C8-2,0PUR-M12FS	8	2		no	30	1
22260728	AB-C8-5,0PUR-M12FS	8	5		no	30	1
22260729	AB-C8-10,0PUR-M12FS	8	10		no	30	1
22262186	AB-C8-15,0PUR-M12FS	8	15		no	30	-

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16



# UNITRONIC® SENSOR M12

		/	(m)	Design	LED	(V)	PU
22260141	AB-C8-2,0PUR-M12FA	8	2		no	30	1
22260615	AB-C8-5,0PUR-M12FA	8	5		no	30	1
22260616	AB-C8-10,0PUR-M12FA	8	10		no	30	1

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

## UNITRONIC® SENSOR M12



(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16