

UNITRONIC® SENSOR SH M12

M12 plug/socket on free conductor end, shielded

/ , M12 , PUR , 3-, 4-, 5- . M12 , A- IP65 / IP67 / IP68 ,

www.lappgroup.com/assemblyfinder 가



Lapp



Space-saving due to compact dimensions.

(가)

가 가

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® SENSOR SH M12

UV-

DIN VDE 0472
UL : E249137
: UL 1581 FT-2

: 0,34 mm²

Colour-code: 3-pin: bn (1), bu (3), bk (4) 4-pin: bn (1), wh (2), bu (3), bk (4) 5-pin: bn (1), wh (2), bu (3), bk (4), gy (5)
: PUR,

ETIM 5:	ETIM 5.0 Class-ID: EC001855
	ETIM 5.0 Class: -
ETIM 6:	ETIM 6.0 Class-ID: EC001855
	ETIM 6.0 Class :
:	: CuSn : Ni/Au ,
	: TPU, ,
:	: 5 x
	: 10 x
가:	IP65/IP67
():	Plug/socket -25°C to +90°C
	-25°C ~ +80°C
	-5°C ~ +80°C
:	A-Standard
(A):	4 A

가 VAT 가 가 . (.) 가 .
UL-Zertifizierungen sind dem Datenblatt zu entnehmen

(23.04.2024)

UNITRONIC® SENSOR SH M12

		/	(m)	Design	LED	(V)	PU
22260453	AB-C3-M12MS-2,0PUR-SH	3	2		no	250	1
22260454	AB-C3-M12MS-5,0PUR-SH	3	5		no	250	1
22260455	AB-C3-M12MS-10,0PUR-SH	3	10		no	250	1
22260450	AB-C3- 2,0PUR-M12FS-SH	3	2		no	250	1
22260451	AB-C3- 5,0PUR-M12FS-SH	3	5		no	250	1
22262086	AB-C3- 6,0PUR-M12FS-SH	3	6		no	250	1
22262077	AB-C3- 7,0PUR-M12FS-SH	3	7		no	250	1
22260452	AB-C3-10,0PUR-M12FS-SH	3	10		no	250	1
22260071	AB-C3- 2,0PUR-M12FA-SH	3	2		no	250	1
22260072	AB-C3- 5,0PUR-M12FA-SH	3	5		no	250	1
22260073	AB-C3-10,0PUR-M12FA-SH	3	10		no	250	1
22261099	AB-C4-M12MS-0,5PUR-SH	4	0.5		no	250	1
22260375	AB-C4-M12MS-1,5PUR-SH	4	1.5		no	250	1
22260459	AB-C4-M12MS-2,0PUR-SH	4	2		no	250	1
22260460	AB-C4-M12MS-5,0PUR-SH	4	5		no	250	1
22260461	AB-C4-M12MS-10,0PUR-SH	4	10		no	250	1
22261067	AB-C4-M12MS-20,0PUR-SH	4	20		no	250	1
22260369	AB-C4-M12MS-25,0PUR-SH	4	25		no	250	1
22262125	AB-C4-M12MA-2,0P	4	2		no	250	1

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® SENSOR SH M12

		/	(m)	Design	LED	(V)	PU
	UR-SH						
22260456	AB-C4- 2,0PUR-M12FS-SH	4	2		no	250	1
22262126	AB-C4- 3,0PUR-M12FS-SH	4	3		no	250	1
22260457	AB-C4- 5,0PUR-M12FS-SH	4	5		no	250	1
22260458	AB-C4-10,0PUR-M12FS-SH	4	10		no	250	1
22261100	AB-C4-15,0PUR-M12FS-SH	4	15		no	250	1
22260823	AB-C4-20,0PUR-M12FS-SH	4	20		no	250	1
22261061	AB-C4-25,0PUR-M12FS-SH	4	25		no	250	1
22260160	AB-C4-30,0PUR-M12FS-SH	4	30		no	250	1
22260074	AB-C4- 2,0PUR-M12FA-SH	4	2		no	250	1
22260855	-	4	3		no	250	-
22260675	AB-C4- 5,0PUR-M12FA-SH	4	5		no	250	1
22260680	AB-C4-10,0PUR-M12FA-SH	4	10		no	250	1
22260374	AB-C4-20,0PUR-M12FA-SH	4	20		no	250	1
22262170	AB-C4-30,0PUR-M12FA-SH	4	30		no	250	1
22262171	AB-C4-50,0PUR-M12FA-SH	4	50		no	250	1
22260465	AB-C5-M12MS-2,0PUR-SH	5	2		no	60	1
22260441	AB-C5-M12MS-3,0PUR-SH	5	3		no	60	1
22260466	AB-C5-M12MS-5,0PUR-SH	5	5		no	60	1
22260467	AB-C5-M12MS-10,0PUR-SH	5	10		no	60	1

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03_16

UNITRONIC® SENSOR SH M12

		/	(m)	Design	LED	(V)	PU
22261064	AB-C5-M12MS-25,0P UR-SH	5	25		no	60	1
22261004	AB-C5-M12MA-2,0P UR-SH	5	2		no	60	1
22260462	AB-C5- 2,0PUR- M12FS-SH	5	2		no	60	1
22262136	AB-C5- 3,0PUR- M12FS-SH	5	3		no	60	1
22260463	AB-C5- 5,0PUR- M12FS-SH	5	5		no	60	1
22260464	AB-C5-10,0PUR- M12FS-SH	5	10		no	60	1
22261057	AB-C5-20,0PUR- M12FS-SH	5	20		no	60	1
22260946	AB-C5- 2,0PUR- M12FA-SH	5	2		no	60	1
22260714	AB-C5- 5,0PUR- M12FA-SH	5	5		no	60	1
22260991	AB-C5-10,0PUR- M12FA-SH	5	10		no	60	1
22260594	AB-C5-20,0PUR- M12FA-SH	5	20		no	60	1
22262173	AB-C8-M12MS-3,0P UR-SH	8	3		no	30	1
22260733	AB-C8-M12MS-5,0P UR-SH	8	5		no	30	1
22262189	AB-C8-M12MS-10,0P UR-SH	8	10		no	30	1
22262130	AB-C8-3,0PUR- M12FS-SH	8	3		no	30	1
22262005	AB-C8-20,0PUR- M12FS-SH	8	20		no	30	1
22261000	AB-C8-15,0PUR- M12FA-SH	8	15		no	30	1
22262191	AB-C8-20,0PUR- M12FA-SH	8	20		no	30	1
22260902	AB-C4-M12MS-2,0P	4	2	-	no	250	-

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

UNITRONIC® SENSOR SH M12

		/	(m)	Design	LED	(V)	PU
	UR-M12FS-SH						
22260903	AB-C4-M12MS-5,0P UR-M12FS-SH	4	5	-	no	250	-
22260821	AB-C5-M12MS-1,0P UR-M12FS-SH	5	1	-	no	60	-
22262203	AB-C5-M12MS-2,0P UR-M12FS-SH	5	2	-	no	60	-
22260822	AB-C5-M12MS-10,0P UR-M12FS-SH	5	10	-	no	60	-
22262082	AB-C5-M12MA-3,0P UR-M12FA-SH	5	3	Angled-angled	no	60	-
22262085	AB-C5-M12MA-4,0P UR-M12FA-SH	5	4	Angled-angled	no	60	-
22261063	AB-C8-M12MS-2,0P UR-M12FS-SH	8	2	-	no	30	-
22260282	AB-C8-M12MS-5,0P UR-M12FS-SH	8	5	-	no	30	-
22260283	AB-C8-M12MS-10,0P UR-M12FS-SH	8	10	-	no	30	-

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16