

EPIC® SENSOR M12

M12

, 가 M12 ()



Lapp



가

IDC

가

Easy connection with proven screw clamp connection

4, 5

8-

(IDC : insulation displacement contacts)

LABS frei

ETIM 5:

ETIM 5.0 Class-ID: EC002062

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC002062

ETIM 6.0 Class :

:

: CuZn

: CuSnZn

가:

IP 65/IP 67 (IDC)

IP 67 ()

():

/ -25 ° C ~ + 80 ° C (IDC) -40 ° C ~ + 85 ° C

(22.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® SENSOR M12

: ()
A-Standard
(A): 4 A
2 A (8-pin)

가 VAT 가 가 .

EPIC® SENSOR M12

		/		(mm ²)	Cable diameter in mm	(V)	PU
22260132	AB-C4-M12MS-F0,34	4	IDC	0.14 - 0.34	3.5 - 6	125	1
22260134	AB-C4-M12MS-F0,75	4	IDC	0.34 - 0.75	4 - 8	250	1
22260649	AB-C4-M12MS-PG7	4		0.25 - 0.75	4 - 6	250	1
22260995	AB-C4-M12MS-PG9	4		0.25 - 0.75	6 - 8	250	1
22260129	AB-C5-M12MS-PG7	5		0.25 - 0.75	4 - 6	60	1
22260651	AB-C5-M12MS-PG9	5		0.25 - 0.75	6 - 8	60	1
22260996	AB-C5-M12MS-PG9-SKINTOP®	5		0.25 - 0.75	6 - 8	60	1
22260135	AB-C5-M12MS-PG9-SH	5		0.25 - 0.75	6 - 8	60	1
22260825	AB-C8-M12MS-PG9-SH	8		0.25 - 0.75	6 - 8	30	1
22260647	AB-C4-M12MA-PG7	4		0.25 - 0.75	4 - 6	250	1
22260130	AB-C5-M12MA-PG7	5		0.25 - 0.75	4 - 6	60	1
22260648	AB-C5-M12MA-PG9	5		0.25 - 0.75	6 - 8	60	1
22262023	AB-C5-M12MA-PG9-SKINTOP®	5		0.25 - 0.75	6 - 8	60	1
22262108	AB-C5-M12MA-PG7-SH	5		0.25 - 0.75	4 - 6	60	1
22260131	AB-C4-M12FS-F0,34	4	IDC	0.14 - 0.34	3.5 - 6	125	1
22260133	AB-C4-M12FS-F0,75	4	IDC	0.34 - 0.75	4 - 8	250	1
22260640	AB-C4-M12FS-PG7	4		0.25 - 0.75	4 - 6	250	1
22260641	AB-C4-M12FS-PG9	4		0.25 - 0.75	6 - 8	250	1
22260127	AB-C5-M12FS-PG7	5		0.25 - 0.75	4 - 6	60	1
22260644	AB-C5-M12FS-PG9	5		0.25 - 0.75	6 - 8	60	1
22260997	AB-C5-M12FS-PG9-SKINTOP®	5		0.25 - 0.75	6 - 8	60	1
22260136	AB-C5-M12FS-	5		0.25 - 0.75	6 - 8	60	1

EPIC® SENSOR M12

		/		(mm ²)	Cable diameter in mm	(V)	PU
	PG9-SH						
22260826	AB-C8-M12FS-PG9-SH	8		0.25 - 0.75	6 - 8	30	1
22260636	AB-C4-M12FA-PG7	4		0.25 - 0.75	4 - 6	250	1
22260128	AB-C5-M12FA-PG7	5		0.25 - 0.75	4 - 6	60	1
22260638	AB-C5-M12FA-PG9	5		0.25 - 0.75	6 - 8	60	1
22262024	AB-C5-M12FA-PG9-SKINTOP®	5		0.25 - 0.75	6 - 8	60	1
22262109	AB-C5-M12FA-PG7-SH	5		0.25 - 0.75	4 - 6	60	1

EPIC® SENSOR M12



(22.02.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16