

EPIC® SENSOR M8

M8

M8 ()



Easy connection with proven screw clamp connection

IDC 가
가

3 4-
, (IDC)
LABS frei

ETIM 5:

ETIM 5.0 Class-ID: EC002062

ETIM 5.0 :

ETIM 6:

ETIM 6.0 Class-ID: EC002062

(23.04.2024)



EPIC® SENSOR M8

:
 가:
 ():
 :
 (A):

ETIM 6.0 Class :
 : CuZn : Au ()
 IP 65/IP 67 (IDC)
 IP 68 ()
 IP 67 ()
 /
 -25°C +80°C (IDC)
 -25°C +85°C ()
 -40°C +85°C ()
 A-Standard
 4 A

가 VAT 가 가 .

(23.04.2024)

EPIC® SENSOR M8

		/		(mm ²)	Cable diameter in mm	(V)	PU
22260993	AB-C3-M8MS-F0,25	3	IDC	0.08 - 0.25	2.5 - 5	60	1
22260985	AB-C3-M8MS-F0,5	3	IDC	0.25 - 0.5	2.5 - 5	60	1
22260043	AB-C4-M8MS-F0,25	4	IDC	0.08 - 0.25	2.5 - 5	60	1
22260044	AB-C4-M8MS-F0,5	4	IDC	0.25 - 0.5	2.5 - 5	60	1
22260120	AB-C3-M8MS	3		0.14 - 0.5	3.5 - 5	60	1
22260121	AB-C4-M8MS	4		0.14 - 0.5	3.5 - 5	60	1
22262025	AB-C3-M8MS-M-0,34-SH	3		0.14 - 0.5	3.5 - 5.5	60	1
22262027	AB-C4-M8MS-M-0,34-SH	4		0.14 - 0.5	3.5 - 5	60	1
22262110	AB-C3-M8MA	3		0.14 - 0.5	3.5 - 5	60	1
22262111	AB-C4-M8MA	4		0.14 - 0.5	3.5 - 5	60	1
22260994	AB-C3-M8FS-F0,25	3	IDC	0.08 - 0.25	2.5 - 5	60	1
22260986	AB-C3-M8FS-F0,5	3	IDC	0.25 - 0.5	2.5 - 5	60	1
22260045	AB-C4-M8FS-F0,25	4	IDC	0.08 - 0.25	2.5 - 5	60	1
22260046	AB-C4-M8FS-F0,5	4	IDC	0.25 - 0.5	2.5 - 5	60	1
22260125	AB-C3-M8FS	3		0.14 - 0.5	3.5 - 5	60	1
22260126	AB-C4-M8FS	4		0.14 - 0.5	3.5 - 5	60	1
22262026	AB-C3-M8FS-M-0,34-SH	3		0.14 - 0.5	3.5 - 5.5	60	1
22262028	AB-C4-M8FS-M-0,34-SH	4		0.14 - 0.5	3.5 - 5.5	60	1
22262112	AB-C3-M8FA	3		0.14 - 0.5	3.5 - 5	60	1
22262113	AB-C4-M8FA	4		0.14 - 0.5	3.5 - 5	60	1

(23.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16