

# UNITRONIC® SENSOR Valve-M12

M12

/ , M12 , PUR , 3 , LED, A, B, C, IP65 / IP67



Lapp



Space-saving due to compact dimensions.

LED (Z ), PE (AD )  
 ( )  
 (2 LED, / )

LABS frei

Cable design:  
 3 x 0.5 mm<sup>2</sup> (28 x 0.15 mm)

(01.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16

# UNITRONIC® SENSOR Valve-M12

5 x 0.5 mm<sup>2</sup> (28 x 0,15mm)

1, 2, /  
 1, 2, 3, 4, /  
 : PUR,  
 :  
 4.5mm  
 5.3mm

ETIM 5:

ETIM 5.0 Class-ID: EC001855  
 ETIM 5.0 Class: -

ETIM 6:

ETIM 6.0 Class-ID: EC001855  
 ETIM 6.0 Class :

:  
 : CuSn : Ni/Au ,  
 : TPU, ,

가:

IP65/IP67

( ):

-20°C +85°C

-25°C +90°C

: -40°C to +80°C, ( ) -20°C to +80°

:

A-Standard

(A):

4 A

가 VAT 가 가 ( . ) 가 .  
 가 VAT 가 가 .

UNITRONIC® SENSOR Valve-M12

		/	(m)	LED	(V)	PU
A (18 mm)						
22260550	AB-C3-M12MS-0,3PUR-A-1L-S	3	0.3	1 LED	24	1
22260551	AB-C3-M12MS-0,6PUR-A-1L-S	3	0.6	1 LED	24	1
22260552	AB-C3-M12MS-1,0PUR-A-1L-S	3	1	1 LED	24	1
22260553	AB-C3-M12MS-2,0PUR-A-1L-S	3	2	1 LED	24	1
A(18mm)						
22260573	AB-C5-M12MS-0,3PUR-AD-2L	5	0.3	2 LEDs	24	1
22260572	AB-C5-M12MS-0,6PUR-AD-2L	5	0.6	2 LEDs	24	1
22260571	AB-C5-M12MS-1,0PUR-AD-2L	5	1	2 LEDs	24	1
22260570	AB-C5-M12MS-2,0PUR-AD-2L	5	2	2 LEDs	24	1
B (10 mm)						
22260558	AB-C3-M12MS-0,3PUR-B-1L-S	3	0.3	1 LED	24	1
22260559	AB-C3-M12MS-0,6PUR-B-1L-S	3	0.6	1 LED	24	1
22260560	AB-C3-M12MS-1,0PUR-B-1L-S	3	1	1 LED	24	1
22260561	AB-C3-M12MS-2,0PUR-B-1L-S	3	2	1 LED	24	1
BI (11 mm)						
22260554	AB-C3-M12MS-0,3PUR-BI-1L-S	3	0.3	1 LED	24	1
22260555	AB-C3-M12MS-0,6PUR-BI-1L-S	3	0.6	1 LED	24	1
22260556	AB-C3-M12MS-1,0PUR-BI-1L-S	3	1	1 LED	24	1
22260557	AB-C3-M12MS-2,0PUR-BI-1L-S	3	2	1 LED	24	1
C (8 mm)						
22260566	AB-C3-M12MS-0,3PUR-C-1L-S	3	0.3	1 LED	24	1
22260567	AB-C3-M12MS-0,6PUR-	3	0.6	1 LED	24	1

(01.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03\_16

UNITRONIC® SENSOR Valve-M12

		/	(m)	LED	(V)	PU
	C-1L-S					
22260568	AB-C3-M12MS-1,0PUR-C-1L-S	3	1	1 LED	24	1
22260569	AB-C3-M12MS-2,0PUR-C-1L-S	3	2	1 LED	24	1
CI (9.4 mm)						
22260562	AB-C3-M12MS-0,3PUR-CI-1L-S	3	0.3	1 LED	24	1
22260563	AB-C3-M12MS-0,6PUR-CI-1L-S	3	0.6	1 LED	24	1
22260564	AB-C3-M12MS-1,0PUR-CI-1L-S	3	1	1 LED	24	1
22260565	AB-C3-M12MS-2,0PUR-CI-1L-S	3	2	1 LED	24	1

(01.05.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16