

(J)-H(ST)H...BD

(J)-H(ST)H...BD - , , 가 , , ,



가 () .
- (TP) (Crosstalk)

가 , , ,

Flame retardant acc. to DIN VDE 0472-804/08.83, Test method C
EN 50267-2-1/-2

, 5 가 ,

(J)-H(ST)H...BD

(), : (RAL 3000)

ETIM 5:	ETIM 5.0 Class-ID: EC000829
	ETIM 5.0 : /
ETIM 6:	ETIM 6.0 Class-ID: EC000829
	ETIM 6.0 Class :
:	VDE 0815, T10
:	. 120 nF/km
:	K1: 300 pF/100 m
:	K9-12: 100 pF/100 m
:	: 8 x
:	Core/core: 800 V
:	Core/screen: 800 V
:	0.6 mm: . 130 ohm/km
:	0.8 mm: . 73.2 ohm/km
:	0.6 mm: 0.28 mm ²
:	0.8 mm: 0.50 mm ²
:	Occasional flexing: -5°C ~ +50°C
:	: -30°C +70°C

, 가 가 . (.) 가 .
www.lappkabel.de/en/cable-standradlengths
: 30 kg or 250 m,

가 VAT 가 가 .

(24.04.2024)



(J)-H(ST)H...BD

	() x () x (mm)	(mm)	(kg/km)	(kg/km)
(J)-H(ST)H...BD				
30017798	2 x 2 x 0.8	7	25	77

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16