

(J)-Y(ST)Y...LG

(J)-Y(ST)Y...LG - , 가 PVC ,



() " "
- (TP) (Crosstalk)

2 (2x2x0.8)
: IEC 60332-1-2

PVC
PVC (), : (RAL 3000)

ETIM 5: ETIM 5.0 Class-ID: EC000829
ETIM 5.0 : /
ETIM 6: ETIM 6.0 Class-ID: EC000829
ETIM 6.0 Class :

(J)-Y(ST)Y...LG

:	VDE 0815, T10
:	(800 Hz): K1: 80% 300 pF/100m
in:	0.8 mm: 0.50 mm ²
/ :	0.8 mm: 1.1 dB/km
:	:
:	10 x
:	Core/core: 800 V
:	Core/screen: 800 V
:	. 73.2 Ohm/km
:	Occasional flexing: -5°C ~ +50°C
:	: -30°C +70°C

가 가 (.) 가 .
www.lappkabel.de/en/cable-standradlengths

: 30 kg or 250 m,

가 VAT 가 가 .



(J)-Y(ST)Y...LG

	() x () x (mm)	(mm)	(kg/km)	(kg/km)
(J)-Y(ST)Y...LG				
1708001	1 x 2 x 0.8	6	11	40
1708002	2 x 2 x 0.8	7	21	60
1708004	4 x 2 x 0.8	9	41	100
1708010	10 x 2 x 0.8	13.5	102	220

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16