

# J-Y(ST)Y...LG Indoor Cable

DIN VDE 0815

J-Y(ST)Y...LG , VDE 0815



- (TP) (Crosstalk )

가 : , 가 , ; ( , ) ; ; 가 : , 가 , ; 가 .

2 :  
: IEC 60332-1-2

DIN VDE 0815  
J-Y(ST)Y...LG

PVC

Outer sheath made of PVC  
Outer sheath colour: grey (similar to pebble grey/ RAL 7032)

(24.04.2024)

©2024 Lapp Group - all rights reserved.  
<http://lappkorea.lappgroup.com>  
data sheet

PN 0456 / 02\_03.16

# J-Y(ST)Y...LG Indoor Cable

ETIM 5:	ETIM 5.0 Class-ID: EC000829
	ETIM 5.0 : /
ETIM 6:	ETIM 6.0 Class-ID: EC000829
	ETIM 6.0 Class :
:	VDE 0815, T10
:	(800 Hz): K1: 80% 300 pF/100m
in:	0.6 mm: 0.28 mm <sup>2</sup>
	0.8 mm: 0.50 mm <sup>2</sup>
/ :	0.6 mm: 1.7 dB/km
	0.8 mm: 1.1 dB/km
:	: 10 x
:	Core/core: 800 V
	Core/screen: 800 V
:	0.6 mm: . 130 ohm/km
	0.8 mm: . 73.2 ohm/km
:	Occasional flexing: -5°C ~ +50°C
	: -30°C +70°C

가 가 ( . ) 가 .  
[www.lappkabel.de/en/cable-standradlengths](http://www.lappkabel.de/en/cable-standradlengths)  
 : 30 kg or 250 m,

가 VAT 가 가 .

J-Y(ST)Y...LG Indoor Cable

	( )	(mm)	[kg/km]	[kg/km]
J-Y(ST)Y...LG 0.6 mm				
1591301	2	5.5	13	40
1591302	3	6.3	18	50
1591303	4	6.7	24	60
1591304	5	7.2	30	70
1591305	6	7.5	35	80
1591306	8	8	46	90
1591307	10	9	58	110
1591308	12	9.5	71	130
1591310	16	10.5	93	160
1591311	20	11	116	190
1591312	24	11.5	139	220
1591313	30	13	172	280
1591315	50	17	286	430
1591318	100	23	568	850
J-Y(ST)Y...LG 0.8 mm				
1591500	1	6	11	40
1591501	2	7	21	60
1591502	3	8.5	31	80
1591503	4	9	41	100
1591505	6	10.5	62	140
1591506	8	11.5	82	170
1591507	10	13	102	220
1591508	12	14	123	250
1591511	20	16.5	204	380

(24.04.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02\_03.16