

EPIC® POWER LS1 D6 TWIST()

EPIC[®] LS1 , TWIST

TWIST
, 1/4
Made in Germany



CE UK CA



(22.07.2024)

EPIC® POWER LS1 D6 TWIST()



SKINTOP®



70%
EMC

EPIC POWER LS1

가, A1,A3,F6,F7,G4,G5

ETIM 5:	ETIM 5.0 Class-ID: EC002635
	ETIM 5.0 class : ()
ETIM 6:	ETIM 6.0 Class-ID: EC002635
	ETIM 6.0 Class : ()
(V):	630 V (2 mm)
	250 V (1 mm)
:	6 kV (2 mm)
	4 kV (1 mm)
(A):	26A/3+PE+4, 25A/5+PE(2mm)
	7 A (1 mm)
:	3
:	< 4 mOhm
:	
/ :	3+PE+4(2mm/1mm)
	5+PE(2mm)
:	: 0.5 - 4.0 mm ² (2 mm contacts)
	: 0.14 - 1.0 mm ² (1 mm contacts)
:	:
	: PA,

(22.07.2024)



EPIC® POWER LS1 D6 TWIST()

가:	:	:	FPM
	:	:	IP68 (10h/1m)
	:	:	500
	:	:	-25°C ~+125°C

가 VAT 가 가 .

(22.07.2024)



EPIC® POWER LS1 D6 TWIST()

	Article description		Clamping range min	Clamping range max	Clamping range in mm		Packaging unit
LS1 D6 , , 6 ,							
24441279	LS1 D6	6	8.5	11	8.5 - 11	5+PE	5
24441280	LS1 D6	-	8.5	11	8.5 - 11	5+PE	20
24441281	LS1 D6	6	10.5	15.5	10.5 - 15.5	5+PE	5
24441282	LS1 D6	-	10.5	15.5	10.5 - 15.5	5+PE	20
24441283	LS1 D6	6	7.5	15.5	7.5 - 15.5	5+PE	5
LS1 D6 , , 8 ,							
24441285	LS1 D6	8	8.5	11	8.5 - 11	3+PE+4	5
24441286	LS1 D6	-	8.5	11	8.5 - 11	3+PE+4	20
24441287	LS1 D6	8	10.5	15.5	10.5 - 15.5	3+PE+4	5
24441288	LS1 D6	-	10.5	15.5	10.5 - 15.5	3+PE+4	20
24441289	LS1 D6	8	7.5	15.5	7.5 - 15.5	3+PE+4	5
24441290	LS1 D6	-	7.5	15.5	7.5 - 15.5	3+PE+4	20

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16