

EPIC® POWER M23 INSERTS

EPIC POWER M23 Inserts



CE UK EAC
CA EAC



(22.07.2024)

EPIC® POWER M23 INSERTS



SKINTOP®



For individual fitting with sockets or male contacts.

Inserts for sockets and inserts for male contacts fit equally in D6 and F6 housings and can be exchanged as desired (housings available separately).

For manufacturing an EPIC® POWER M23 circular connector.

For use with housings of the EPIC® POWER M23 series.

ETIM 5:	ETIM 5.0 Class-ID: EC002635
	ETIM 5.0 class : ()
(V):	630 V (2 mm) 250 V (1 mm)
:	6 kV (2 mm) 4 kV (1 mm)
(A):	26A/3+PE+4, 25A/5+PE(2mm) 7 A (1 mm)
:	3
:	< 4 mOhm
/ :	3+PE+4(2mm/1mm) 5+PE(2mm)
:	: 0.5 - 4.0 mm ² (2 mm contacts) : 0.14 - 1.0 mm ² (1 mm contacts)
:	PA
:	500
:	-25°C ~+125°C

(22.07.2024)



EPIC® POWER M23 INSERTS

가 VAT 가 가 .

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16



EPIC® POWER M23 INSERTS

	Article description	Clamping range in mm		Packaging unit
24441170	EPIC POWER M23 3+PE+4 FEMALE	-	3+PE+4	20
24441171	EPIC POWER M23 3+PE+4 MALE	-	3+PE+4	20
24441168	EPIC POWER M23 5+PE FEMALE	-	5+PE	20
24441169	EPIC POWER M23 5+PE MALE	-	5+PE	20

(22.07.2024)

©2024 Lapp Group - all rights reserved.

<http://lappkorea.lappgroup.com>

data sheet

PN 0456 / 02_03.16

EPIC® POWER M23 INSERTS



(22.07.2024)

EPIC® POWER M23 INSERTS



(22.07.2024)